

Safety Instructions

**Levelflex M**

**FMP40, FMP43, FMP45**

**HART, PROFIBUS PA, FOUNDATION Fieldbus**

Ex emb [ia] IIC T6...T1

NEPSI GYJ101291

**XA00376F-C**



**en** - Safety instructions for electrical apparatus for explosion-hazardous areas.

**zh** - 爆炸环境中电气仪表的安全指南。



# Levelflex M

## FMP40, FMP43, FMP45

english

### HART, PROFIBUS PA, FOUNDATION Fieldbus

**Associated  
Documentation**

This document is an integral part of the following Operating Instructions:  
HART: BA242F/00 (FMP40), BA357F/00 (FMP43), BA279F/00 (FMP45)  
PROFIBUS PA: BA243F/00 (FMP40), BA358F/00 (FMP43), BA280F/00 (FMP45)  
FOUNDATION Fieldbus: BA244F/00 (FMP40), BA359F/00 (FMP43), BA281F/00 (FMP45)  
The Operating Instructions which are supplied and correspond to the device type apply.

**Designation**

Explanation of the labelling and type of protection can be found in the explosion protection brochure.

---

**Designation of explosion protection****Ex emb [ia] IIC T6...T1**




Fig. 1

XA376en01

<b>Power supply</b>	Ue ≤ 32 V DC Um ≤ 250 V AC	Connection compartment (Ex e)	Observe instructions *2
---------------------	-------------------------------	-------------------------------	-------------------------

<b>Application</b>	Zone 1: FMP40, FMP43, FMP45 Zone 0/1: only FMP45	Probe and housing in Zone 1 Probe in Zone 0 and housing in Zone 1
<b>Type of protection</b>	Ex emb [ia] IIC T6...T1	
<b>Max. working pressure</b>	Dependent on the probe	
<b>Process temperature</b>	Dependent on the probe	

<b>Housing T12</b>	-40 °C ≤ Tu ≤ +75 °C	Optionally with or without VU331 display and operating module
--------------------	----------------------	---

**Safety instructions:  
Installation**

- Install the device according to the manufacturer's instructions and any other valid standards and regulations.
- Do not operate the device outside the specified electrical, thermal and mechanical parameters.
- The housing of transmitter is equipped with a ground terminal; users must ensure that it is reliably connected to ground during installation and use.
- The relationship between the permitted ambient temperature for the electronics housing, dependent on the range of application, and the temperature classes is shown in the tables (Tab. 1a FMP40, Tab. 1b FMP43, Tab. 1c FMP45).
- After aligning (rotating) the housing, retighten the fixing screw (see Operating Instructions).
- Continuous duty temperature of the cable  $\geq T_a + 5 \text{ K}^{*1}$ .
- Replace cable glands only with identical parts <sup>\*1</sup>.
- Connection compartment cover: "Do not open under voltage in explosive atmospheres" <sup>\*2</sup>.
- Do not open the connection compartments under voltage in an explosive atmosphere.
- Only install the devices in media for which the wetted materials have sufficient durability.
- Install the device to exclude any mechanical damage or friction during the application. Pay particular attention to flow conditions and fittings.
- Changes in electrical and mechanical parts of the equipment could harm the type of explosion protection and are not allowed for the user.
- The safety parameters of the circuit of the externally connected monitor are as follows:  
 $U_o = 4.2 \text{ V}$ ,  $I_o = 34 \text{ mA}$ ,  $P_o = 36 \text{ mW}$ ,  $C_o = 4 \text{ }\mu\text{F}$ ,  $L_o = 5 \text{ mH}$   
 When this product is equipped with an external monitor, it must also conform to the following specifications:  
 $U_o \leq U_i$ ,  $I_o \leq I_i$ ,  $P_o \leq P_i$ ,  $C_o \geq C_i + C_c$ ,  $L_o \geq L_i + L_c$   
 Note:  
 –  $U_i$ ,  $I_i$  and  $P_i$  represent the maximum input voltage, maximum input current and maximum input power of the monitor respectively.  
 –  $C_i$  and  $L_i$  represent the maximum internal equivalent capacitance and inductance of the monitor respectively.  
 –  $C_c$  and  $L_c$  represent the distributed capacitance and distributed inductance of cable.

**FMP43**

- The device with separable probe in separated mode shall be closed by protective cover.

**Zone 1 - Application**

Tab. 1a **FMP40**

Temperature class with or without VU331 display	Maximum permitted medium temperature (process connection) Probe in Zone 1	Maximum permitted ambient temperature at the electronics housing (electronics housing in Zone 1) dependent on the medium temperature				
		With ¾" probe, compact	With ¾" probe and remote electronics / spacer tube	With 1½" probe, compact	With 1½" probe and remote electronics / spacer tube	With remote electronics / spacer hose
T6	+ 75 °C + 60 °C	55 °C 60 °C	55 °C 60 °C	55 °C 60 °C	55 °C 60 °C	60 °C 60 °C
T5	+ 95 °C + 75 °C	70 °C 75 °C	70 °C 75 °C	70 °C 75 °C	70 °C 75 °C	75 °C 75 °C
T4	+130 °C + 75 °C	65 °C 75 °C	70 °C 75 °C	65 °C 75 °C	70 °C 75 °C	75 °C 75 °C
T3 (functional) <sup>*3</sup> , T2, T1	+150 °C + 75 °C	65 °C 75 °C	70 °C 75 °C	65 °C 75 °C	70 °C 75 °C	75 °C 75 °C

Note: permitted probe temperature range must be observed  
<sup>\*3</sup> functional = limited by maximum permitted probe temperature

Tab. 1b **FMP43**

Temperature class with or without VU331 display	Maximum permitted medium temperature (process connection) Probe in Zone 1	Maximum permitted temperature at the electronics housing (electronics housing in Zone 1) dependent on the medium temperature	
		Compact or compact, detachable	Remote, cable, detachable
T6	+ 75 °C + 60 °C	55 °C 60 °C	60 °C 60 °C
T5	+ 95 °C + 75 °C	70 °C 75 °C	75 °C 75 °C
T4	+130 °C + 75 °C	65 °C 75 °C	75 °C 75 °C
T3, T2, T1 (functional) <sup>*3</sup>	+150 °C + 75 °C	65 °C 75 °C	75 °C 75 °C

Note: the applicable temperature of probe must be within their specified limits

<sup>\*3</sup> functional = max. permissible process temperature

Tab. 1c **FMP45**

Temperature class with or without VU331 display	Maximum permitted medium temperature (process connection) Probe in Zone 1	Maximum permitted ambient temperature at the electronics housing (electronics housing in Zone 1) dependent on the medium temperature		
		Type A, (XT version)	Type B (HT version)	With remote electronics / spacer hose
T6	+ 75 °C + 60 °C	58 °C 60 °C	59 °C 60 °C	60 °C 60 °C
T5	+ 95 °C + 75 °C	73 °C 75 °C	74 °C 75 °C	75 °C 75 °C
T4	+130 °C + 75 °C	71 °C 75 °C	73 °C 75 °C	75 °C 75 °C
T3 (functional) <sup>*3</sup>	+150 °C + 75 °C	69 °C 75 °C	72 °C 75 °C	75 °C 75 °C
T3	+195 °C + 75 °C	67 °C 75 °C	70 °C 75 °C	75 °C 75 °C
T2 (functional) <sup>*3</sup>	+250 °C + 75 °C	64 °C 75 °C	68 °C 75 °C	75 °C 75 °C
T2 (functional) <sup>*3</sup>	+290 °C + 75 °C	280 °C: 62 °C 75 °C	67 °C 75 °C	75 °C 75 °C
T1 (functional) <sup>*3</sup>	+400 °C + 75 °C	not allowed	63 °C 75 °C	75 °C 75 °C

Note: permitted probe temperature range must be observed

<sup>\*3</sup> functional = limited by maximum permitted probe temperature

**Safety instructions:  
Zone 0 (only FMP45)**

- Only operate devices in potentially explosive vapour/air mixtures under atmospheric conditions \*4:  
 $-20\text{ °C} \leq T \leq +60\text{ °C}$   
 $0.8\text{ bar} \leq p \leq 1.1\text{ bar}$
- If no potentially explosive mixtures are present, the transmitters may be operated under other atmospheric conditions in accordance with the manufacturer's specifications.
- Only install the devices in media for which the wetted materials have sufficient durability.
- For installation, use and maintenance of the device, users must also observe the requirements stated in the Operating Instructions and the standards:
  - GB50257-1996: "Code for construction and acceptance of electric device for explosion atmospheres and fire hazard electrical equipment installation engineering".
  - GB3836.13-1997: "Electrical apparatus for explosive gas atmospheres, Part 13: Repair and overhaul for apparatus used in explosive gas atmospheres".
  - GB3836.15-2000: "Electrical apparatus for explosive gas atmospheres, Part 15: Electrical installations in hazardous area (other than mines)".
  - GB3836.16-2006: "Electrical apparatus for for explosive gas atmospheres, Part 16: Inspection and maintenance of electrical installation (other than mines)".

**Zone 0 - Application**

Tab. 2  
**FMP45**

Temperature class with or without VU331 display	Maximum permitted medium temperature (process connection) Probe in Zone 0 *4	Maximum permitted ambient temperature at the electronics housing (electronics housing in Zone 1) dependent on the medium temperature		
		Type A, (XT version)	Type B (HT version)	With remote electronics / spacer hose
T6	+60 °C	60 °C	60 °C	60 °C
T5, T4, T3, T2, T1	+60 °C	75 °C	75 °C	75 °C





# Levelflex M

## FMP40, FMP43, FMP45

文  
中

HART, PROFIBUS PA, FOUNDATION Fieldbus (基金会现场总线)

### 相关资料

本文档是下列操作手册的组成部分：

HART：BA242F/00 (FMP40)、BA357F/00 (FMP43)、BA279F/00 (FMP45)

PROFIBUS PA：BA243F/00 (FMP40)、BA358F/00 (FMP43)、BA280F/00 (FMP45)

FOUNDATION Fieldbus (基金会现场总线)：BA244F/00 (FMP40)、BA359F/00 (FMP43)、BA281F/00 (FMP45)

根据用户订购仪表的具体型号所提供的相应操作手册。

### 名称

防爆标志和防护类型说明请查询防爆手册。

防爆代号

Ex emb [ia] IIC T6...T1




图 1

电源	$U_e \leq 32 \text{ V DC}$ $U_m \leq 250 \text{ V AC}$	接线柜 (Ex e)	遵循指南 *2
----	---	---------------	---------

应用	区域 1: FMP40、FMP43、FMP45 区域 0/1: 仅 FMP45	探针和外壳在区域 1 中 探针在区域 0 中, 外壳在区域 1 中
防护类型	Ex emb [ia] IIC T6...T1	
最大工作压力	取决于探针	
过程温度	取决于探针	

T12 外壳	$-40 \text{ °C} \leq T_u \leq +75 \text{ °C}$	可选带有或不带有 VU331 显示屏和 操作模块
--------	---	-----------------------------

**安全指南：  
安装**

- 按照制造商的说明及其它有效标准和规定来安装设备。
- 使用设备时请勿超出指定的电、热和机械参数。
- 变送器的外壳装备有接地端子；在安装和使用的过程中，用户应确保该端子可靠接地。
- 电子部件外壳的允许环境温度（取决于应用范围）与温度等级之间的关系如下表所示（表 1a FMP40，表 1b FMP43，表 1c FMP45）。
- 在对齐（旋转）外壳后，重新拧紧固定螺丝（参见操作说明）。
- 电缆持续工作温度  $\geq T_a + 5 \text{ K}^{*1}$ 。
- 只能使用相同的部件更换电缆栓塞  $^{*1}$ 。
- 接线柜盖：“请勿在爆炸性空气中带电压打开盖子”  $^{*2}$ 。
- 在爆炸性空气环境中使用仪表时，请勿带电压开启接线柜。
- 当仪表的受潮部件对介质具有足够耐久性时，才可将仪表安装于介质中。
- 仪表的安装方式应避免在应用期间遭受任何机械损坏或磨损。  
请尤其注意流量状况和液罐装置。
- 改动设备的电气和机械部件会降低防爆保护的类型，用户请勿擅自改动。
- 外接监视器电路的安全参数如下所示：  
 $U_o = 4.2 \text{ V}$ ， $I_o = 34 \text{ mA}$ ， $P_o = 36 \text{ mW}$ ， $C_o = 4 \mu\text{F}$ ， $L_o = 5 \text{ mH}$   
当本产品配备外接监视器时，必须符合下列技术规范：  
 $U_o \leq U_i$ ， $I_o \leq I_i$ ， $P_o \leq P_i$ ， $C_o \geq C_i + C_c$ ， $L_o \geq L_i + L_c$   
注意：  
-  $U_i$ 、 $I_i$  和  $P_i$  分别代表监视器的最大输入电压、最大输入电流和最大输入功率。  
-  $C_i$  和  $L_i$  分别代表监视器的最大内部等效电容和电感。  
-  $C_c$  和  $L_c$  代表电缆的分布电容和分布电感。

**FMP43**

- 带有独立探针的处于独立模式的设备应以防护盖盖上。

**区域 1 - 应用**

表 1a **FMP40**

温度等级， 带有或不带 VU331 显示屏	最大允许输入温度 (工艺连接件) 探针在区域 1 中	电子部件外壳处的最大允许环境温度 (电子部件外壳在区域 1 内) 取决于输入温度				
		带有 3/4" 探针， 紧凑型	带有 3/4" 探针和远程 电子部件 / 隔离管	带有 1 1/2" 探针， 紧凑型	带有 1 1/2" 探针和远程 电子部件 / 隔离管	带有远程 电子部件 / 隔离软管
T6	+ 75 °C + 60 °C	55 °C 60 °C	55 °C 60 °C	55 °C 60 °C	55 °C 60 °C	60 °C 60 °C
T5	+ 95 °C + 75 °C	70 °C 75 °C	70 °C 75 °C	70 °C 75 °C	70 °C 75 °C	75 °C 75 °C
T4	+130 °C + 75 °C	65 °C 75 °C	70 °C 75 °C	65 °C 75 °C	70 °C 75 °C	75 °C 75 °C
T3 (功能型) $^{*3}$ ， T2, T1	+150 °C + 75 °C	65 °C 75 °C	70 °C 75 °C	65 °C 75 °C	70 °C 75 °C	75 °C 75 °C

提示： 必须遵守允许的探针温度范围

$^{*3}$  功能型 = 受限于允许的最大探针温度

表 1b FMP43

温度等级， 带有或不带 VU331 显示屏	最大允许输入温度 (工艺连接件) 探针在区域 1 中	电子部件外壳处的最大允许温度 (电子部件外壳在区域 1 内) 取决于输入温度	
		紧凑型或紧凑拆卸型	远程，电缆，拆卸型
T6	+ 75 °C + 60 °C	55 °C 60 °C	60 °C 60 °C
T5	+ 95 °C + 75 °C	70 °C 75 °C	75 °C 75 °C
T4	+130 °C + 75 °C	65 °C 75 °C	75 °C 75 °C
T3, T2, T1 (功能型)* <sup>3</sup>	+150 °C + 75 °C	65 °C 75 °C	75 °C 75 °C

提示： 探针的适用温度必须位于规定的限制范围之内

\*<sup>3</sup> 功能型 = 最大允许的过程温度

表 1c FMP45

温度等级， 带有或不带 VU331 显示屏	最大允许输入温度 (工艺连接件) 探针在区域 1 中	电子部件外壳处的最大允许环境温度 (电子部件外壳在区域 1 内) 取决于输入温度		
		类型 A (XT 版本)	类型 B (HT 版本)	带有远程电子部件 / 隔离软管
T6	+ 75 °C + 60 °C	58 °C 60 °C	59 °C 60 °C	60 °C 60 °C
T5	+ 95 °C + 75 °C	73 °C 75 °C	74 °C 75 °C	75 °C 75 °C
T4	+130 °C + 75 °C	71 °C 75 °C	73 °C 75 °C	75 °C 75 °C
T3 (功能型)* <sup>3</sup>	+150 °C + 75 °C	69 °C 75 °C	72 °C 75 °C	75 °C 75 °C
T3	+195 °C + 75 °C	67 °C 75 °C	70 °C 75 °C	75 °C 75 °C
T2 (功能型)* <sup>3</sup>	+250 °C + 75 °C	64 °C 75 °C	68 °C 75 °C	75 °C 75 °C
T2 (功能型)* <sup>3</sup>	+290 °C + 75 °C	280 °C: 62 °C 75 °C	67 °C 75 °C	75 °C 75 °C
T1 (功能型)* <sup>3</sup>	+400 °C + 75 °C	不允许	63 °C 75 °C	75 °C 75 °C

提示： 必须遵守允许的探针温度范围

\*<sup>3</sup> 功能型 = 受限于允许的最大探针温度

**安全指南：**  
**区域 0 (仅 FMP45)**

- 只有在下列大气条件下才能在有爆炸可能的蒸汽 / 空气混合物中操作设备 \*4：  
-20 °C ≤ T ≤ +60 °C  
0.8 bar ≤ p ≤ 1.1 bar
- 如果不存在可能爆炸的混合物，则变送器可在符合制造商技术规范的其他大气条件下运行。
- 当仪表的受潮部件对介质具有足够耐久性时，才可将仪表安装于介质中。
- 在安装、使用和维护产品时，用户必须遵守操作手册和下列标准中的规定：
  - GB50257-1996：“电气设备安装工程 爆炸和火灾危险环境电气装置施工及验收规范”
  - GB3836.13-1997：“爆炸性气体环境用电气设备 第 13 部分：爆炸性气体环境用电气设备的检修”。
  - GB3836.15-2000：“爆炸性气体环境用电气设备 第 15 部分：危险场所电气安装 (煤矿除外)”。
  - GB3836.16-2006：“爆炸性气体环境用电气设备 第 16 部分：电气装置的检查和维护 (煤矿除外)”。

**区域 0 - 应用**

表 2  
**FMP45**

温度等级， 带有或不带 VU331 显示屏	最大允许输入温度 (工艺连接件) 探针在区域 0 中 *4	电子部件外壳处的最大允许环境温度 (电子部件外壳在区域 1 内) 取决于输入温度		
		类型 A (XT 版本)	类型 B (HT 版本)	带有远程电子部件 / 隔离软管
T6	+60 °C	60 °C	60 °C	60 °C
T5, T4, T3, T2, T1	+60 °C	75 °C	75 °C	75 °C





[www.endress.com/worldwide](http://www.endress.com/worldwide)

---

**Endress+Hauser** 

People for Process Automation

---

