



Manufacturer Information

for users regarding software updates
(following the NAMUR recommendation 53)

1 Type of device

- Field device / signal processing device
- Monitoring- / operation system / hand held terminal etc.
- Modem / interface

Manufacturer : Endress+Hauser GmbH+Co. KG, 79689 Maulburg
 Device : Cerabar S / Deltabar S
 Type : PMC71, PMP71/75, PMD70/75, FMD76/77/78
 FOUNDATION Fieldbus (FF)
 Previous software version : 02.00.02 /DevRev 5

How can the previous software version number be identified:

via FieldCare or on-site: Group Selection -> Operating Menu ->
 Transmitter Info -> Transmitter Data -> Software Version

2 Firmware/Software

New firm-/software version : 03.00.00 / DevRev 6

Description of the modification in comparison with the predecessor version:

Transducer Blocks:
 New Level Mode "Easy".
 New Flow Block (only for Deltabar S)
 Function Blocks:
 New Integrator Block
 New Digital Input Block for diagnostic Information
 Enhancement of Analog Input Block (binary Outputs for limit alarms)
 In general:
 Display with 3 push buttons for complete on-site navigation
 Electronic Name Plate (ENP)
 Macro-cycle time set on 100ms.

3 Compatibility

Is the newly installed firmware/software compatible with the operating tools?

- Yes
- No, description:

New DD available for FF-Konfigurator Tool (see www.endress.com or www.fieldbus.org).
 New DTM for Fieldcare (see www.endress.com).

Not compatible anymore with the Tof-Tool and Commuwin.



Manufacturer Information

for users regarding software updates
(following the NAMUR recommendation 53)

Is a firm-/software update generally recommended?

Yes, reasons:

The firm-/software update can be performed by means of ...

No, reasons:

The new software enhances the transmitter behaviour and offers an easier parametrization in the measuring mode Level.

4 Instruction manual

Is a new instruction manual necessary due to the modification of the firm-/software?

Yes

No

Which manual corresponds to the new firm-/software:

Device	Communication options	Manual	Marking
Cerabar S	FF	Cerabar S PMC71, PMP71/75 Pressure Transmitter	KA1025P/00/en BA302P/00/en/08.08 SW 3.00.zz
–	–	–	–
Deltabar S	FF	Deltabar S PMD70/75, FMD76/77/78 Differential Pressure Transmitter	KA1024P/00/en BA301P/00/en/08.08 SW 3.00.zz
Cerabar S/ Deltabar S/ Deltapilot S	FF	Detailed Description of Functionality	BA303P/00/en/08.08

The new instruction manuals can be referred in Internet:

<http://www.endress.com>

- area „DOWNLOAD“

- declaration of the device and kind of manual



Manufacturer Information

for users regarding software updates
(following the NAMUR recommendation 53)

5 Price

Change in price of device in comparison with the predecessor version?

- Yes, new list price and update costs (without installation) are enclosed
- No