



# Technical Information

# iTEMP<sup>®</sup> TMT125

Temperature transmitter with FOUNDATION Fieldbus<sup>™</sup> protocol. 8 input channels for resistance thermometers, thermocouples, resistance and voltage transmitters.





#### Application

- Temperature transmitter with 8 input channels and FOUNDATION Fieldbus<sup>™</sup> protocol for converting various input signals into digital output signals
- Input:
- Resistance thermometers (RTD) Thermocouples (TC) Resistance transmitters  $(\Omega)$
- Voltage transmitters (mV)
- DIN rail mounting as per IEC 60715 and with aluminum housing for field operation

### Your benefits

- Universal temperature transmitter for up to 8 input signals
- Inputs for RTD in 2-wire, 3-wire and 4-wire technology
- Every input can be configured individually
- Sensor monitoring: cable open circuit, short-circuit and wiring error
- Device hardware fault recognition for reliable operation and easy maintenance
- Galvanic isolation between fieldbus and sensor inputs and between the input channels
- Connection of thermocouples to all inputs possible
- Data transfer via FOUNDATION Fieldbus<sup>™</sup> H1
- Transducer block 'concentrator' and Multiple Analog Input Block (MAI) allow for effective and fast configuration of the relevant parameters
- Approvals:
- FM IS, NI
- ATEX EEx ia, EEx na

for intrinsically safe installation in zone 1 and as associated apparatus in zone 2  $\,$ 

- Independent installation of connected temperature sensors in zone 0
- FISCO-compliant in accordance with IEC 60079-27 for easy measuring point layout in hazardous areas
- FOUNDATION Fieldbus<sup>™</sup> ITK 4.61




### Function and system design

Measuring principle

Electronic monitoring and conversion of various input signals in industrial temperature measurement.

Measuring system

Device architecture



System integration via FOUNDATION Fieldbus<sup>TM</sup>

The 8-channel temperature transmitter transfers both converted signals from resistance temperature measuring sensors and thermocouples as well as resistance and millivolt signals via FOUNDATION Fieldbus<sup>TM</sup>. The device is powered via the FOUNDATION Fieldbus<sup>TM</sup> H1 bus and can be installed as intrinsically safe apparatus in zone 1 or as associated apparatus in zone 2 of hazardous areas. The device is available as a version for mounting on a DIN rail as per IEC 60715 and installed in a field housing for use in the field. The data is transferred via the following function blocks:

- 8 x Analog Input (AI) and
- 1 x Multiple Analog Input (MAI)

In addition, the Transducer block 'concentrator' allows for effective configuration of the parameters relevant for the temperature measurement. Every input can be individually configured and the individual inputs have a potential separation from each other of  $U = 600 V_{ss}$ .

Sensor diagnoses such as cable open circuit, short-circuit, wiring error and device hardware error are supported. LED displays provide information about the operating status and error status.

	Input
Measured variable	Temperature (temperature linear transmission behavior), resistance and voltage.
Measuring range	The transmitter records different measuring ranges depending on the sensor connection and input signals.

Type of inp	out	Resistance thermometer (RTD)		
Туре	Standard	Measuring range limits	Maximum measured error (accuracy)	Temperature drift
Pt50	IEC 60751 (ITS90)	-200 to 850 °C (-328 to 1562 °F)	± 0.77 °C (± 1.39 °F)	± 0.0010 °C/K
Pt100	$(\alpha = 0.00385)$	-200 to 850 °C (-328 to 1562 °F)	± 0.33 °C (± 0.59 °F)	± 0.0010 °C/K
Pt100	JIS C 1604–1989 ( $\alpha = 0.003916$ )	-200 to 630 °C (-328 to 1166 °F)	± 0.33 °C (± 0.59 °F)	± 0.0010 °C/K
Pt200		-200 to 850 °C (-328 to 1562 °F)	± 0.33 °C (± 0.59 °F)	± 0.0010 °C/K
Pt500	IEC 60751 (ITS90) ( $\alpha = 0.00385$ )	-200 to 850 °C (-328 to 1562 °F)	± 0.31 °C (± 0.56 °F)	± 0.0010 °C/K
Pt1000	(a = 0.00000)	-200 to 850 °C (-328 to 1562 °F)	± 0.31 °C (± 0.56 °F)	± 0.0010 °C/K
Ni100	DIN 43760-1987 (α = 0.006180)	-60 to 250 °C (-76 to 482 °F)	± 0.18 °C (± 0.32 °F)	± 0.0010 °C/K
Ni120	Minco Standard	-80 to 320 °C (-112 to 608 °F)	± 0.18 °C (± 0.32 °F)	± 0.0010 °C/K
Ni200	DIN 43706-1987 ( $\alpha = 0.006180$ )	-60 to 250 °C (-76 to 482 °F)	± 0.18 °C (± 0.32 °F)	± 0.0010 °C/K
Cu10	SAMA RC21-4-1966 ( $\alpha = 0.003923$ )	-70 to 150 °C (-94 to 302 °F)	± 2.99 °C (± 5.38 °F)	± 0.0010 °C/K

### Thermocouples $(TC)^{1)}$

_			Maximum measured	Temperature drift		
Туре	Standard	Measuring range limits	error (accuracy)	Range	Deviation	
В		300 to 600 °C (572 to 1112 °F) 600 to 1200 °C (1112 to 2192 °F) 1200 to 1800 °C (2192 to 3272 °F)	± 3.32 °C (± 5.98 °F) ± 1.77 °C (± 3.19 °F) ± 1.08 °C (± 1.94 °F)	300 to 600 °C (572 to 1112 °F) 600 to 1200 °C (1112 to 2192 °F) 1200 to 1800 °C (2192 to 3272 °F)	± 0.0060 °C/K ± 0.0131 °C/K ± 0.0242 °C/K	
E		-200 to -50 °C (-328 to -58 °F) -50 to 1000 °C (-58 to 1832 °F)	± 0.42 °C (± 0.76 °F) ± 0.31 °C (± 0.56 °F)	-200 to -50 °C (-328 to -58 °F) -50 to 200 °C (-58 to 392 °F) 200 to 1000 °C (392 to 1832 °F)	± 0.0070 °C/K ± 0.0036 °C/K ± 0.0203 °C/K	
J		-200 to 0 °C (-328 to 32 °F) 0 to 1000 °C (32 to 1832 °F)	± 0.48 °C (± 0.86 °F) ± 0.31 °C (± 0.56 °F)	-200 to 0 °C (-328 to 32 °F) 0 to 200 °C (32 to 392 °F) 200 to 1000 °C (392 to 1832 °F)	± 0.0072 °C/K ± 0.0039 °C/K ± 0.0243 °C/K	
К	IEC	-200 to 0 °C (-328 to 32 °F) 0 to 1372 °C (32 to 2501 °F)	± 0.68 °C (± 1.22 °F) ± 0.43 °C (± 0.77 °F)	-200 to 0 °C (-328 to 32 °F) 0 to 500 °C (32 to 932 °F) 500 to 1372 °C (932 to 2501 °F)	± 0.0077 °C/K ± 0.0097 °C/K ± 0.0323 °C/K	
N	60584-1	-200 to -100 °C (-328 to -148 °F) -100 to 500 °C (-148 to 932 °F) 500 to 1300 °C (932 to 2372 °F)	± 1.03 °C (± 1.85 °F) ± 0.54 °C (± 0.97 °F) ± 0.39 °C (± 0.70 °F)	-200 to -100 °C (-328 to -148 °F) -100 to 500 °C (-148 to 932 °F) 500 to 1300 °C (932 to 2372 °F)	± 0.0080 °C/K ± 0.0088 °C/K ± 0.0264 °C/K	
R		0 to 350 °C (32 to 662 °F) 350 to 1768 °C (662 °F to 3214 °F)	± 1.93 °C (± 3.47 °F) ± 1.16 °C (± 2.09 °F)	0 to 350 °C (32 to 662 °F) 350 to 800 °C (662 to 1472 °F) 800 to 1768 °C (1472 to 3214 °F)	± 0.0057 °C/K ± 0.0129 °C/K ± 0.0338 °C/K	
S		0 to 550 °C (32 to 1022 °F) 550 to 1768 °C (1022 to 3214 °F)	± 1.92 °C (± 3.46 °F) ± 1.15 °C (± 2.07 °F)	0 to 550 °C (32 to 1022 °F) 550 to 800 °C (1022 to 1472 °F) 800 to 1768 °C (1472 to 3214 °F)	± 0.0094 °C/K ± 0.0135 °C/K ± 0.0355 °C/K	
Т		-200 to -50 °C (-328 to -58 °F) -50 to 400 °C (-58 to 752 °F)	± 0.66 °C (± 1.19 °F) ± 0.35 °C (± 0.63 °F)	-200 to -50 °C (-328 to -58 °F) -50 to 200 °C (-58 to 392 °F) 200 to 400 °C (392 to 752 °F)	± 0.0071 °C/K ± 0.0035 °C/K ± 0.0067 °C/K	

_			Maximum measured	Temperature drift		
Туре	Standard	Measuring range limits	error (accuracy)	Range	Deviation	
W5Re W24Re	ASTM E988-96	0 to 800 °C (32 to 1472 °F) 800 to 2000 °C (1472 to 3632 °F)	± 0.80 °C (± 1.45 °F) ± 1.05 °C (± 1.89 °F)	0 to 800 °C (32 to 1472 °F) 800 to 2000 °C (1472 to 3632 °F)	± 0.0151 °C/K ± 0.0552 °C/K	
<ul> <li>Cold junction internal</li> <li>Accuracy of cold junction ± 0.5 °C (± 0.9 °F)</li> </ul>						

#### Resistance transmitter $\boldsymbol{\Omega}$

Measuring range limits	Maximum measured error (accuracy)	Temperature drift
0 to 650 Ω	$\pm$ 115 m $\Omega$	$\pm$ 6 m $\Omega/K$
0 to 1300 Ω	$\pm$ 230 m $\Omega$	$\pm$ 6 m $\Omega/K$
0 to 2600 Ω	$\pm$ 460 m $\Omega$	$\pm 13 \text{ m}\Omega/\text{K}$
0 to 5200 Ω	$\pm$ 920 m $\Omega$	$\pm 26 \text{ m}\Omega/\text{K}$


### Voltage transmitter (mV)

Measuring range limits	Maximum measured error (accuracy)	Temperature drift	
-100 to 150 mV	$\pm$ 20 $\mu V$	$\pm 2 \ \mu V/K$	

# Output

Output signal	FOUNDATION Fieldbus™ H1, IEC 61158-2, galvanically isolated
	Physical Layer profile: Profile type 511 (FISCO) Profile type 111 (Entity)
	ITK version 4.61
Linearization/transmission behavior	Temperature linear, resistance linear, voltage linear
Galvanic isolation	$\hat{U} = 375 \text{ V AC} \text{ (fieldbus/inputs)}$
Filter	50 or 60 Hz
Min. current consumption	$\leq$ 23 mA
Switch-on delay	approx. 20 s
Function blocks	<ul> <li>Resource block (RS): <ol> <li>x RS</li> </ol> </li> <li>Function blocks (execution time max. 40 ms, macro cycle ≤ 500 ms): <ol> <li>x Analog Input block (AI)</li> <li>x Multiple Analog Input block (MAI)</li> </ol> </li> <li>Transducer blocks (TB): <ol> <li>x sensor TB</li> <li>x concentrator TB</li> </ol> </li> </ul>
FDE (Fault Disconnect Equipment)	6.7 mA

1) Grounding of all thermocouples possible



U = 9 to 32 V DC, reverse polarity protection

# Power supply

Supply voltage

Cable entries (field housing)

	Sen	sor connection	FOUNDATIO	N Fieldbus <sup>TM</sup> connection
Cable connections, material	Cable gland	Cable diameter mm (in) / across flats	Cable gland	Cable diameter mm (in) / across flats
Terminals and cable guide, nickeled brass	M16 x 1.5	5 to 10 (0.19 to 0.39") / 20	M20 x 1.5	7 to 12 (0.28 to 0.47") / 24

Response time	< 1 s per channel
Reference operating conditions	+25 °C ± 5 K (+77 °F ± 9 °F)
Maximum measured error	Accuracy for the various types of input, see $\rightarrow$ $\geqq$ 3, under "Type of input".
Influence of ambient temperature (temperature drift)	Temperature drift for the various types of input, see $\rightarrow \geqq$ 3, under "Type of input".
Influence of cold junction	± 0.5 °C (± 0.9 °F)
Linearization	<ul> <li>RTD input 0.03 °C (0.054 °F)</li> <li>TC input 0.1 °C (0.18 °F)</li> </ul>
Internal update time	For all sensor types $\leq 1$ s
Potential separation	600 V <sub>SS</sub> (input/input)

# Performance characteristics

# Installation conditions

Installation instructions	Installation/mounting location
	Wall or cabinet mounting on DIN rail as per IEC 60715. A mounted device in aluminum field housing for field
	instrumentation is optionally available (for dimensions, see $\rightarrow \mathbb{B}$ 8).


# **Environment conditions**

Ambient temperature	Type of connection	Temperature range		
		Hazardous area	Non-hazardous area	
	Field housing; cable guide, nickeled brass	40 to +70 °C (-40 to +158 °F)	40 to + 95 °C ( 40 to + 195 °E)	
	Without field housing	40 t0 +70 °C (-40 t0 +158 F)	-40 to +85 °C (-40 to +185 °F)	
Storage temperature	-40 to +80 °C (-40 to +176 °F)			
Relative humidity	$\leq$ 95 % not condensing, valid for the DIN rail version			
Climate class	Tested as per IEC 60068-2-30, meets the requirements regarding class C1-C3 in accordance with IEC 60721-4-3			
Degree of protection	Mounting on a DIN rail IP 20		IP 20	
8 F	thould and bit a bit that		-	


Shock resistance	Impact resistance as per IEC 60068-2-27					
	Mounting on a DIN rail			15g, 11 ms		
	Mounting in aluminum field housir	ıg		15g, 11 ms		
Vibration resistance	As per IEC 60068-2-6					
	Mounting on a DIN rail			5g, 10 to 150 Hz		
	Mounting in aluminum field housing				10g, 10 to 150 Hz	
Electromagnetic compatibility (EMC)	This recommendation is a consis and in process control systems a				in laboratories	
	ESD (electrostatic discharge)	IEC 61000-4-2	6 kV cont., 8 kV air			
	Electromagnetic fields	IEC 61000-4-3	0.08 to 4 GHz		10 V/m	
	Burst (fast transients)	IEC 61000-4-4	1 kV			
	Surge	IEC 61000-4-5	1 kV asym.			
	Conducted RF	IEC 61000-4-6	0.01 to 80 MHz		10 V	

# Mechanical construction

#### Design, dimensions



Housing for DIN rail as per IEC 60715; specifications in mm (in)



Dimensions of field housing; specifications in mm (in) Item A: Securing with M6 bolt Item B: Grounding, shielding point

Weight	<ul> <li>DIN rail version: 360 g (12.7 oz)</li> <li>Installed in field housing: 1.8 kg (3.97 lb)</li> </ul>
Material	<ul> <li>DIN rail housing: polycarbonate (PC)</li> <li>Field housing: AlSi12 (Cu), EN573 (Si 1.2% - proportion), anodized</li> <li>Nameplate: polyester (PE)</li> </ul>
Terminals	<ul> <li>Plug-in terminals, sensor and fieldbus cables up to max. 2.5 mm<sup>2</sup> (14 AWG)</li> <li>Specifications for cable glands and diameters →  <sup>1</sup>/<sub>2</sub> 5.</li> </ul>

#### **Display elements** 6 3 2 1 4 5 CHANNEL ERROI Simulate Enal Write Lock Not Used ۲ ۲ (+)AAAA MAAP MP MMM CH3 CH5 CH7 <u>30000</u> 0000 Bus 00 $\bigcirc$ 0000 O OC $\bigcirc$ MAAA AAAA MAAA CH8 CH6 CH2 CH4 0000 0000 0000 $\bigcirc$ $(\mathbf{F})$ Endress+Hauser DEVICE ID 452 (Ex) G EEx nA II T4 G EEx nL IIC T4 TMT125 Ex PTB 05 ATEX xxxx II2 (1G/D)G EEx ia IIC T4 II(1) GD [EEx ia ] IIC Made in G 87484 s 3 Ser.No.: TAG No.: 0123456789101 1019876543210 inst. per XA056R/09/a3/XX.XX FISCO according to IEC TS 60079-2 40°C < Ta < 70°C ∆ Č€ $\bigcirc$ $\bigcirc$ Operating and display elements of the temperature transmitter Item 1: LED illuminated in green indicates 'In operation' Item 2: LED Illuminated in red or flashing red indicates "Communication error": hardware or fieldbus error Item 3: LED flashing red indicates 'Channel error': cable open circuit or overshooting Item 4: DIP switch for hardware settings Item 5: Segregation plate for mounting in hazardous area (device zone 2 - sensors zone 1 or zone 0) Item 6: Service interface **Operating elements** DIP switch for setting the parameters: hardware write protection and simulation (precondition for FOUNDATION Fieldbus<sup>TM</sup> simulation mode) Service interface, only relevant for service technicians! **Remote operation** The configuration of FOUNDATION Fieldbus™ functions and device-specific parameters is done via the fieldbus interface. You can obtain special configuration and operating programs from various manufacturers for these purposes.

### Human interface

CE-Mark	The device meets the legal requirements of the EC directives. Endress+Hauser confirms that the device has been successfully tested by applying the CE mark.		
Hazardous area approvals	For further details on the available Ex versions (ATEX, CSA, FM, etc.), please contact your nearest Endress+Hauser sales organisation. All relevant data for hazardous areas can be found in separate Ex documentation. If required, please request copies from us or your Endress+Hauser sales organisation.		
Other standards and guidelines	<ul> <li>IEC 60529: Degree of protection provided by housing (IP-code)</li> <li>IEC 61158-2: Fieldbus for use in industrial control systems</li> <li>IEC 60068-2-27 and IEC 60068-2-6: Shock and vibration tests</li> <li>IEC 61326: Electromagnetic compatibility (EMC requirements)</li> <li>NAMUR Standards working group for measurement and control technology in the chemical industry (www.namur.de)</li> </ul>		
Certification FOUNDATION Fieldbus <sup>™</sup>	<ul> <li>The temperature transmitter has successfully passed all test procedures and is certified and registered by the Fieldbus Foundation. The device thus meets all the requirements of the specifications following:</li> <li>Certified according to FOUNDATION Fieldbus<sup>™</sup> specification</li> <li>The device meets all the specifications of the FOUNDATION Fieldbus<sup>™</sup> H1</li> <li>Interoperability Test Kit (ITK), revision status 4.61 (device certification no. available on request): the device can also be operated with certified devices of other manufacturers</li> <li>Physical layer conformance test of the FOUNDATION Fieldbus<sup>™</sup></li> </ul>		

# Certificates and approvals

### Ordering information

### Product structure

This information provides an overview of the order options available. The information is not exhaustive, however, and may not be fully up to date. **More detailed** information is available from your local Endress+Hauser representative.

TMT125	iTE	iTEMP <sup>®</sup> TMT125, multi channel transmitter						
	Ap	Approval						
	Α	Non-hazardous area						
	В	ATEX				D)G EEx ia IIC T4; EEx ia IIC		
	С	FM IS				2/ABCD/T4 , II, III/1/ABCDEFG		
	D	FMC IS				2/ABCD/T4 /I, II, III/1/ABCDEFG		
	Е	IEC	Ex	Ex	ia IIC	T4 [Ex ia] IIC		
	F	IEC	Ex	Ex	nA II 1	ſ4		
	1	NE	PSI	[Ex	ia] IIC			
	2	NEPSI Ex nA II T4						
		Co	mmu	inic	ation			
		1	FOL	JND	ATION	Fieldbus		
			Ho	usin	g			
			1	DIN	V rail, I	IEC 60715		
			2	Fiel	ld hous	sing, alu, IP 67, 8x M16 + 1x M20 gland		
		<b>3</b> Field housing, alu, IP 67, 8x M16 gland + 1x plug 7/8" FF						
				Co	nnec	tion		
				1	Screv	v terminal		
					Con	figuration		
					Α	Factory setup		
						Version		
						A Standard		
TMT125-		1		1	Α	A $\leftarrow$ Order code		

# Accessories

Order code		Туре
71005804		Fieldbus connector (FOUNDATION Fieldbus <sup>TM</sup> ), for M20 $\rightarrow$ 7/8"
TMT125A-		Field housing 8xM16 + 1x M20 gland Field housing 8xM16 + 1x plug 7/8" FOUNDATION Fieldbus™

The following accessories are contained in the scope of delivery:

- Multi-language Brief Operating Instructions as hard copy
- Operating Instructions on CD-ROM

# Documentation

□Operating Instructions iTEMP<sup>®</sup> TMT125 (BA240R/09/en) on CD-ROM and associated Brief Operating Instructions iTEMP<sup>®</sup> TMT125 (KA241R/09) as hard copy

□ Ex supplementary documentation:

ATEX II 2(1G/D)G; II (1)GD; II 3G: XA056R/09/a3

#### **Instruments International**

Endress+Hauser Instruments International AG Kaegenstrasse 2 4153 Reinach Switzerland

Tel.+41 61 715 81 00 Fax+41 61 715 25 00 www.endress.com info@ii.endress.com

