Technical Information Proline Prowirl D 200

Vortex flowmeter

Products



Low-cost wafer flange design, available as compact or remote device version

Application

- Preferred measuring principle for wet/saturated/ superheated steam, gases & liquids (also cryogenic)
- For all basic applications and for 1-to-1 replacement of orifice plates

Device properties

- Face-to-face length of 65 mm (2.56 in)
- No flanges
- Low weight
- Display module with data transfer function
- Robust dual-compartment housing
- Plant safety: worldwide approvals (SIL, Haz. area)

Your benefits

- Integrated temperature measurement for mass/energy flow of saturated steam
- Easy alignment of the sensor included centering rings
- High availability proven robustness, resistance to vibrations, temperature shocks & water hammer
- No maintenance lifetime calibration
- Convenient device wiring separate connection compartment
- Safe operation no need to open the device due to display with touch control, background lighting
- Integrated verification Heartbeat Technology™



Table of contents

Document information		Vibration resistance	
Symbols used	3	Electromagnetic compatibility (EMC)	53
Function and system design	3	Process	53
Measuring principle		Medium temperature range	53
Measuring system		Pressure-temperature ratings	53
including of occini vivia vivi		Secondary containment pressure rating	54
Input	6	Pressure loss	55
Measured variable		Thermal insulation	55
Measuring range		Vibrations	55
Operable flow range			
Input signal	8	Mechanical construction	55
		Dimensions in SI units	55
Output	9	Dimensions in US units	62
Output signal	- 1	Weight	66
Signal on alarm		Materials	69
	11		
	12	Operability	71
	17	Operating concept	
	17	Local operation	
Protocol-specific data	17	Remote operation	
		Service interface	74
	23		
Terminal assignment		Certificates and approvals	
Pin assignment, device plug		CE mark	
	25	C-Tick symbol	
	26 26	Ex approval	
P	27	HART certification	
	27	FOUNDATION Fieldbus certification	
	31	Certification PROFIBUS	
	31	Pressure Equipment Directive	
	31	Experience	
Cable specification	31	Other standards and guidelines	77
Overvoltage protection	32		
Performance characteristics	22	Ordering information	78
Reference operating conditions			
	33	Application packages	
	35	Diagnostics functions	
	35	Heartbeat Technology	79
	35	Air and industrial gases	79 79
-		ivaturai yas	13
Installation	36	Accessories	79
5	36		
	36	Communication-specific accessories	
	37	Service-specific accessories	
3	39	System components	
	40		
3	40 41	Supplementary documentation	83
Special mounting instructions	41	Standard documentation	
- .	, ,	Supplementary device-dependent documentation	
Environment		•	
	42	Registered trademarks	Q/ı
	52 52	negistereu trauemarks	U-1
	52		
Degree of protection	74		

2

Document information

Symbols used

Electrical symbols

Symbol	Meaning	Symbol	Meaning
	Direct current	~	Alternating current
≂	Direct current and alternating current	-	Ground connection A grounded terminal which, as far as the operator is concerned, is grounded via a grounding system.
	Protective ground connection A terminal which must be connected to ground prior to establishing any other connections.	♦	Equipotential connection A connection that has to be connected to the plant grounding system: This may be a potential equalization line or a star grounding system depending on national or company codes of practice.

Symbols for certain types of information

Symbol	Meaning
✓	Permitted Procedures, processes or actions that are permitted.
✓	Preferred Procedures, processes or actions that are preferred.
X	Forbidden Procedures, processes or actions that are forbidden.
i	Tip Indicates additional information.
Ţ <u>i</u>	Reference to documentation
A	Reference to page
	Reference to graphic
	Visual inspection

Symbols in graphics


Symbol	Meaning	Symbol	Meaning
1, 2, 3,	Item numbers	1. , 2. , 3	Series of steps
A, B, C,	Views	A-A, B-B, C-C,	Sections
<u>ÉX</u>	Hazardous area	×	Safe area (non-hazardous area)
≋➡	Flow direction		

Function and system design

Measuring principle

Vortex meters work on the principle of the *Karman vortex street*. When fluid flows past a bluff body, vortices are alternately formed on both sides with opposite directions of rotation. These vortices each generate a local low pressure. The pressure fluctuations are recorded by the sensor and converted to

electrical pulses. The vortices develop very regularly within the permitted application limits of the device. Therefore, the frequency of vortex shedding is proportional to the volume flow.



The calibration factor (K-factor) is used as the proportional constant:

A0003939-EN

Within the application limits of the device, the K-factor only depends on the geometry of the device. It is for Re > 20000:

- Independent of the flow velocity and the fluid properties viscosity and density
- Independent of the type of substance under measurement: steam, gas or liquid

The primary measuring signal is linear to the flow. After production, the K-factor is determined in the factory by means of calibration. It is not subject to long-time drift or zero-point drift.

The device does not contain any moving parts and does not require any maintenance.

The capacitance sensor

The sensor of a vortex flowmeter has a major influence on the performance, robustness and reliability of the entire measuring system.

The robust DSC sensor is:

- burst-tested
- tested against vibrations
- tested against thermal shock (thermal shocks of 150 K/s)

The Prowirl uses the tried-and-tested capacitance measuring technology of Endress+Hauser applied in over 300 000 measuring points worldwide.

The DSC (differential switched capacitance) sensor patented by Endress+Hauser has complete mechanical balancing. It only reacts to the measured variable (vortex) and does not react to vibrations. Even in the event of pipe vibrations, the smallest of flows can be reliably measured at low density thanks to the unimpaired sensitivity of the sensor. Thus, the wide turndown is also maintained even in the event of harsh operating conditions. Vibrations up to 1~g at least, at frequencies up to 500~Hz in every axis (X, Y, Z), do not affect the flow measurement. Thanks to its design, the capacitance sensor is also particularly mechanically resistant to temperature shocks and pressure shocks in steam pipelines.


Temperature measurement

Under the order code for "Sensor version", the "Mass flow" option is available. With this option the measuring device can also measure the temperature of the medium.

The temperature is measured via Pt 1000 temperature sensors. These sensors are located in the paddle of the DSC sensor and are therefore in the direct vicinity of the fluid.

Order code for "Sensor version":

- Option 1 "Volume flow, basis"
- Option 2 "Volume flow, high-temperature/low temperature"
- Option 3 "Mass flow (integrated temperature measurement)"



40010720

- 1 Sensor
- 2 Seal
- 3 Order code for "Sensor version", option 1 "Volume flow, basis" and option 2 "Volume flow, high-temperature/low-temperature"
- 4 Order code for "Sensor version", option 3 "Mass flow (integrated temperature measurement)"

Lifelong calibration

Experience has shown that recalibrated Prowirl devices demonstrate a very high degree of stability compared to their original calibration: The recalibration values were all within the original measuring accuracy specifications of the devices.

Various tests and simulation procedures have shown that once the radii of the edges on the bluff body are less than 1 mm (0.04 in), the resulting effect does not have a negative impact on accuracy.

If the radii of the edges on the bluff body do not exceed 1 mm (0.04 in), the following general statements apply (in the case of non-abrasive and non-corrosive media, such as in most water and steam applications):

- The measuring device does not display an offset in the calibration and the accuracy is still quaranteed.
- All the edges on the bluff body have a radius that is typically smaller in size. As the measuring devices are naturally also calibrated with these radii, the measuring device remains within the specified accuracy rating provided that the additional radius that is produced as a result of wear and tear does not exceed 1 mm (0.04 in).

Consequently it can be said that the Prowirl product line offers lifelong calibration if the measuring device is used in non-abrasive and non-corrosive media.

Diagnostic functions

In addition, the device offers extensive diagnostic options, such as tracking fluid and ambient temperatures, extreme flows etc.

The following minimum and maximum values are tracked in the measuring device and saved for diagnostic purposes:

- Frequency
- Temperature
- Velocity
- Pressure


Measuring system

The device consists of a transmitter and a sensor.

Two device versions are available:

- Compact version transmitter and sensor form a mechanical unit.
- Remote version transmitter and sensor are mounted in separate locations.

Transmitter



Device versions and materials:


- Compact or remote version, aluminum coated:
- Aluminum, AlSi10Mg, coated
- Compact or remote version, stainless:
 For maximum corrosion resistance: stainless steel CF-3M (316L, 1.4404)

A0013471 | Con

Configuration:

- Via four-line local display with key operation or via four-line, illuminated local display with touch control and guided menus ("Makeit-run" wizards) for applications
- Via operating tools (e.g. FieldCare)

Sensor



Disc (wafer version):

- Nominal diameter range: DN 15 to 150 (½ to 6")
- Materials: Measuring tubes: stainless steel, 1.4408 (CF3M)

Input

Measured variable

Direct measured variables

Order code for "Sensor version":

- Option 1 "Volume flow, basis" and
- Option 2 "Volume flow, high-temperature/low temperature": Volume flow

Order code for "Sensor version":

Option 3 "Mass flow (integrated temperature measurement)":

- Volume flow
- Temperature

Calculated measured variables

Order code for "Sensor version":

- Option 1 "Volume flow, basis" and
- Option 2 "Volume flow, high-temperature/low temperature":
 - In the case of constant process conditions: Mass flow $^{1)}$ or Corrected volume flow
 - The totalized values for Volume flow, Mass flow ¹⁾, or Corrected volume flow

¹⁾ A fixed density must be entered for calculating the mass flow (**Setup** menu → **Advanced setup** submenu → **External compensation** submenu → **Fixed density** parameter).


Order code for "Sensor version":

- Option 3 "Mass flow (integrated temperature measurement)":
 - Corrected volume flow
 - Mass flow
 - Calculated saturated steam pressure
 - Energy flow
 - Heat flow difference
- Only in combination with order code for "Output; input", bus version HART and PROFIBUS PA:
 - Specific volume
 - Degrees of superheat

Measuring range

The measuring range depends on the fluid and nominal diameter.

Flow velocity



A0027507

- E DN diameter
- v_E Velocity in process pipe
- *v* Bluff body approaching flow velocity (Re is based on this)
- v2 Maximum velocity (applies only to oxygen) $v_2 = v_{max}$
- *v*₃ *Velocity when leaving the measuring device*
- D_i Internal diameter $D_i = D_3$
- D3 Internal diameter $D_3 = D_i$
- d Width of bluff body
- f Vortex shedding frequency
- The Applicator can be used for calculation purposes. $\rightarrow \triangleq 82$

Maximum volume flow	Strouhal number	Reynolds number
$Q_{\max(G)} = V_{\max} \cdot \frac{\pi}{4} D_i^2$	$Sr = \frac{f \cdot d}{v}$	$Re = \frac{\rho \cdot v \cdot D_i}{\mu}$
A0027504	A0027505	A0027506

Lower range value

Depends on the density of the medium and the Reynolds number ($Re_{min} = 5\,000$, $Re_{linear} = 20\,000$). The Reynolds number is dimensionless and indicates the ratio of the inertia force of a fluid to its viscous force. It is used to characterize the flow. The Reynolds number is calculated as follows:

$$Re = \frac{4 \cdot Q \left[m^3/s \right] \cdot \rho \left[kg/m^3 \right]}{\pi \cdot di \left[m \right] \cdot \mu \left[Pa \cdot s \right]} \qquad \qquad Re = \frac{4 \cdot Q \left[ft^3/s \right] \cdot \rho \left[lb/ft^3 \right]}{\pi \cdot di \left[ft \right] \cdot \mu \left[0.001 \text{ cP} \right]}$$

A0003794

Re = Reynolds number; Q = flow; di = internal diameter; μ = dynamic viscosity, ρ = density

DN 15...150
$$\rightarrow v_{\text{min.}} = \frac{6}{\sqrt{\rho [\text{kg/m}^3]}} [\text{m/s}]$$

DN ½...6" $\rightarrow v_{\text{min.}} = \frac{4.92}{\sqrt{\rho [\text{lb/ft}^3]}} [\text{ft/s}]$

10020557

Upper range value

Liquids:

The upper range value must be calculated as follows: $v_{max} = 9$ m/s (30 ft/s) and $v_{max} = 350/\sqrt{\rho}$ m/s (130/ $\sqrt{\rho}$ ft/s)

▶ Use the lower value.

Gas/steam:

Nominal diameter	v_{max}
Standard device: DN 15 (½")	46 m/s (151 ft/s) and 350/ $\sqrt{\rho}$ m/s (130/ $\sqrt{\rho}$ ft/s) (Use the lower value.)
Standard device: DN 25 (1"), DN 40 (1½")	75 m/s (246 ft/s) and 350/ $\sqrt{\rho}$ m/s (130/ $\sqrt{\rho}$ ft/s) (Use the lower value.)
Standard device: DN 50 to 150 (2 to 8")	120 m/s (394 ft/s) and 350/ $\sqrt{\rho}$ m/s (130/ $\sqrt{\rho}$ ft/s) (Use the lower value.) Calibrated range: up to 75 m/s (246 ft/s)



For information on the Applicator $\rightarrow \triangleq 82$

Operable flow range

Up to 45: 1 (ratio between lower and upper range value)

Input signal

Current input

Current input	4-20 mA (passive)
Resolution	1 μΑ
Voltage drop	Typically: 2.2 to 3 V for 3.6 to 22 mA
Maximum voltage	≤35 V
Possible input variables	PressureTemperatureDensity

External measured values

To increase the accuracy of certain measured variables or to calculate the corrected volume flow, the automation system can continuously write different measured values to the measuring device:

- Operating pressure to increase accuracy (Endress+Hauser recommends the use of a pressure measuring device for absolute pressure, e.g. Cerabar M or Cerabar S)
- Medium temperature to increase accuracy (e.g. iTEMP)
- Reference density for calculating the corrected volume flow



- Various pressure transmitters can be ordered from Endress+Hauser: see "Accessories" section
 → 82
- \bullet Please comply with the special mounting instructions when using pressure transmitters $\rightarrow~\cong~41$

It is recommended to read in external measured values to calculate the following measured variables:

- Energy flow
- Mass flow
- Corrected volume flow

8

Current input

HART protocol

The measured values are written from the automation system to the measuring device via the HART protocol. The pressure transmitter must support the following protocol-specific functions:

- HART protocol
- Burst mode

Fieldbuses

The measured values can be written from the automation system to the measuring via:

- FOUNDATION Fieldbus
- PROFIBUS PA

Output

Output signal

Current output

Current output 1	4-20 mA HART (passive)
Current output 2	4-20 mA (passive)
Resolution	< 1 µA
Damping	Adjustable: 0.0 to 999.9 s
Assignable measured variables	 Volume flow Corrected volume flow Mass flow Flow velocity Temperature Calculated saturated steam pressure Total mass flow Energy flow Heat flow difference

Pulse/frequency/switch output

Function	Can be set to pulse, frequency or switch output
Version	Passive, open collector
Maximum input values	 DC 35 V 50 mA For information on the Ex connection values → □ 12
Voltage drop	For ≤ 2 mA: 2 VFor 10 mA: 8 V
Residual current	≤ 0.05 mA
Pulse output	
Pulse width	Adjustable: 5 to 2 000 ms
Maximum pulse rate	100 Impulse/s
Pulse value	Adjustable
Assignable measured variables	 Total volume flow Total corrected volume flow Total mass flow Total energy flow Total heat flow difference

Frequency output	
Output frequency	Adjustable: 0 to 1000 Hz
Damping	Adjustable: 0 to 999 s
Pulse/pause ratio	1:1
Assignable measured variables	 Volume flow Corrected volume flow Mass flow Flow velocity Temperature Calculated saturated steam pressure Steam quality Total mass flow Energy flow Heat flow difference
Switch output	
Switching behavior	Binary, conductive or non-conductive
Switching delay	Adjustable: 0 to 100 s
Number of switching cycles	Unlimited
Assignable functions	■ Off ■ On ■ Diagnostic behavior ■ Limit value — Volume flow — Corrected volume flow — Mass flow — Flow velocity — Temperature — Calculated saturated steam pressure — Steam quality — Total mass flow — Energy flow — Heat flow difference — Reynolds number — Totalizer 1-3 ■ Status ■ Status of low flow cut off

FOUNDATION Fieldbus

Signal encoding	Manchester Bus Powered (MBP)
Data transfer	31.25 KBit/s, Voltage mode

PROFIBUS PA

Signal encoding	Manchester Bus Powered (MBP)
Data transfer	31.25 KBit/s, Voltage mode

Signal on alarm

Depending on the interface, failure information is displayed as follows:

Current output

HART

Device diagnostics	Device condition can be read out via HART Command 48

Pulse/frequency/switch output

Pulse output	
Failure mode	No pulses
Frequency output	
Failure mode	Choose from: Actual value O Hz Defined value: 0 to 1250 Hz
Switch output	
Failure mode	Choose from: Current status Open Closed

FOUNDATION Fieldbus


Status and alarm messages	Diagnostics in accordance with FF-891
Error current FDE (Fault Disconnection Electronic)	0 mA

PROFIBUS PA

Status and alarm messages	Diagnostics in accordance with PROFIBUS PA Profile 3.02
Error current FDE (Fault Disconnection Electronic)	0 mA

Local display

Plain text display	With information on cause and remedial measures
Backlight	Additionally for device version with SD03 local display: red lighting indicates a device error.



Operating tool

- Via digital communication:
 - HART protocol
 - FOUNDATION Fieldbus
 - PROFIBUS PA
- Via service interface

Plain text display	With information on cause and remedial measures
--------------------	---

Additional information on remote operation $\rightarrow~\equiv~72$

Load for current output: 0 to 500 Ω , depending on the external supply voltage of the power supply unit


11

Load

Calculation of the maximum load

Depending on the supply voltage of the power supply unit (U_S), the maximum load (R_B) including line resistance must be observed to ensure adequate terminal voltage at the device. In doing so, observe the minimum terminal voltage

- $R_B \le (U_S U_{term. min})$: 0.022 A $R_B \le 500 \Omega$



■ 1 Load for a compact version without local operation

- 1.1 For order code for "Output", option A "4-20 mA HART"/option B "4-20 mA HART, pulse/frequency/switch output" with Ex i and option C "4-20 mA HART + 4-20 mA analog"
- 1.2 For order code for "Output", option A "4-20 mA HART"/option B "4-20 mA HART, pulse/frequency/switch output" with non-Ex and Ex d

Sample calculation

Supply voltage of the supply unit:

- $-U_{S} = 19 V$
- $U_{term. min}$ = 12 V (measuring device) + 1 V (local operation without lighting) = 13 V

Maximum load: $R_B \le (19 \text{ V} - 13 \text{ V})$: 0.022 A = 273 Ω

The minimum terminal voltage ($U_{\text{term. min}}$) increases if local operation is used (Verweisziel existiert nicht, aber @y.link.required='true').

Ex connection data

Safety-related values

Type of protection Ex d

Order code for "Output"	Output type	Safety-related values
Option A	4-20mA HART	U _{nom} = DC 35 V U _{max} = 250 V
Option B	4-20mA HART	$U_{\text{nom}} = DC 35 V$ $U_{\text{max}} = 250 V$
	Pulse/frequency/switch output	$U_{nom} = DC 35 V$ $U_{max} = 250 V$ $P_{max} = 1 W^{1}$
Option C	4-20mA HART	U _{nom} = DC 30 V
	4-20mA analog	$U_{\text{max}} = 250 \text{ V}$
Option D	4-20mA HART	$U_{\text{nom}} = \text{DC } 35 \text{ V}$ $U_{\text{max}} = 250 \text{ V}$
	Pulse/frequency/switch output	$U_{nom} = DC 35 V$ $U_{max} = 250 V$ $P_{max} = 1 W^{1}$
	4 to 20 mA current input	U _{nom} = DC 35 V U _{max} = 250 V

Order code for "Output"	Output type	Safety-related values
Option E	FOUNDATION Fieldbus	$U_{nom} = DC 32 V$ $U_{max} = 250 V$ $P_{max} = 0.88 W$
	Pulse/frequency/switch output	$U_{nom} = DC 35 V$ $U_{max} = 250 V$ $P_{max} = 1 W^{1}$
Option G	PROFIBUS PA	$U_{nom} = DC 32 V$ $U_{max} = 250 V$ $P_{max} = 0.88 W$
	Pulse/frequency/switch output	$U_{nom} = DC 35 V$ $U_{max} = 250 V$ $P_{max} = 1 W^{1}$

1) Internal circuit limited by R_i = 760.5 Ω

Ex nA type of protection

Order code for "Output"	Output type	Safety-related values
Option A	4-20mA HART	U _{nom} = DC 35 V U _{max} = 250 V
Option B	4-20mA HART	U _{nom} = DC 35 V U _{max} = 250 V
	Pulse/frequency/switch output	$U_{nom} = DC 35 V$ $U_{max} = 250 V$ $P_{max} = 1 W^{1)}$
Option C	4-20mA HART	U _{nom} = DC 30 V
	4-20mA analog	$U_{\text{max}} = 250 \text{ V}$
Option D	4-20mA HART	U _{nom} = DC 35 V U _{max} = 250 V
	Pulse/frequency/switch output	$U_{nom} = DC 35 V$ $U_{max} = 250 V$ $P_{max} = 1 W^{1)}$
	4 to 20 mA current input	U _{nom} = DC 35 V U _{max} = 250 V
Option E	FOUNDATION Fieldbus	$U_{nom} = DC 32 V$ $U_{max} = 250 V$ $P_{max} = 0.88 W$
	Pulse/frequency/switch output	$U_{nom} = DC 35 V$ $U_{max} = 250 V$ $P_{max} = 1 W^{1)}$
Option G	PROFIBUS PA	$U_{nom} = DC 32 V$ $U_{max} = 250 V$ $P_{max} = 0.88 W$
	Pulse/frequency/switch output	$U_{nom} = DC 35 V$ $U_{max} = 250 V$ $P_{max} = 1 W^{1)}$

1) Internal circuit limited by R_i = 760.5 Ω

Type of protection XP

Order code for "Output"	Output type	Safety-related values
Option A	4-20mA HART	U _{nom} = DC 35 V U _{max} = 250 V
Option B	4-20mA HART	$U_{nom} = DC 35 V$ $U_{max} = 250 V$
	Pulse/frequency/switch output	$U_{nom} = DC 35 V$ $U_{max} = 250 V$ $P_{max} = 1 W^{1}$
Option C	4-20mA HART	U _{nom} = DC 30 V
	4-20mA analog	$U_{\text{max}} = 250 \text{ V}$
Option D	4-20mA HART	U _{nom} = DC 35 V U _{max} = 250 V
	Pulse/frequency/switch output	$U_{nom} = DC 35 V$ $U_{max} = 250 V$ $P_{max} = 1 W^{1}$
	4 to 20 mA current input	U _{nom} = DC 35 V U _{max} = 250 V
Option E	FOUNDATION Fieldbus	$U_{nom} = DC 32 V$ $U_{max} = 250 V$ $P_{max} = 0.88 W$
	Pulse/frequency/switch output	$U_{nom} = DC 35 V$ $U_{max} = 250 V$ $P_{max} = 1 W^{1}$
Option G	PROFIBUS PA	$U_{nom} = DC 32 V$ $U_{max} = 250 V$ $P_{max} = 0.88 W$
	Pulse/frequency/switch output	$U_{nom} = DC 35 V$ $U_{max} = 250 V$ $P_{max} = 1 W^{1}$

1) Internal circuit limited by R_i = 760.5 Ω

Intrinsically safe values

Type of protection Ex ia

Order code for "Output"	Output type	Intrinsically safe values
Option A	4-20mA HART	$\begin{split} &U_{i} = DC \ 30 \ V \\ &I_{i} = 300 \ mA \\ &P_{i} = 1 \ W \\ &L_{i} = 0 \ \mu H \\ &C_{i} = 5 \ nF \end{split}$
Option B	4-20mA HART	$\begin{split} &U_{i} = DC \ 30 \ V \\ &I_{i} = 300 \ mA \\ &P_{i} = 1 \ W \\ &L_{i} = 0 \ \mu H \\ &C_{i} = 5 \ nF \end{split}$
	Pulse/frequency/switch output	$ \begin{array}{l} U_i = DC\ 30\ V \\ I_i = 300\ mA \\ P_i = 1\ W \\ L_i = 0\ \mu H \\ C_i = 6\ nF \end{array} $
Option C	4-20mA HART	$U_{i} = DC 30 V$ $I_{i} = 300 mA$ $P_{i} = 1 W$ $L_{i} = 0 \mu H$

Order code for "Output"	Output type	Intrinsically safe values	
	4-20mA analog	$C_i = 30 \text{ nF}$	
Option D	4-20mA HART	$\begin{split} &U_i = DC~30~V\\ &I_i = 300~mA\\ &P_i = 1~W\\ &L_i = 0~\mu H\\ &C_i = 5~nF \end{split}$	
	Pulse/frequency/switch output	$\begin{split} &U_i = DC~30~V\\ &I_i = 300~mA\\ &P_i = 1~W\\ &L_i = 0~\mu H\\ &C_i = 6~nF \end{split}$	
	4 to 20 mA current input	$\begin{split} &U_{i} = DC \ 30 \ V \\ &I_{i} = 300 \ mA \\ &P_{i} = 1 \ W \\ &L_{i} = 0 \ \mu H \\ &C_{i} = 5 \ nF \end{split}$	
Option E	FOUNDATION Fieldbus	$\begin{array}{llllllllllllllllllllllllllllllllllll$	
	Pulse/frequency/switch output	$\label{eq:Ui} \begin{split} &U_{i} = 30 \ V \\ &l_{i} = 300 \ mA \\ &P_{i} = 1 \ W \\ &L_{i} = 0 \ \mu H \\ &C_{i} = 6 \ nF \end{split}$	
Option G	PROFIBUS PA	$\begin{array}{llllllllllllllllllllllllllllllllllll$	
	Pulse/frequency/switch output	$\begin{array}{l} U_i = 30 \ V \\ l_i = 300 \ mA \\ P_i = 1 \ W \\ L_i = 0 \ \mu H \\ C_i = 6 \ nF \end{array}$	

Type of protection Ex ic

Order code for "Output"	Output type	Intrinsically safe values
Option A	4-20mA HART	$\begin{split} &U_i = DC\ 35\ V\\ &I_i = n.a.\\ &P_i = 1\ W\\ &L_i = 0\ \mu H\\ &C_i = 5\ nF \end{split}$
Option B	4-20mA HART	$\begin{split} &U_i = DC\ 35\ V\\ &I_i = n.a.\\ &P_i = 1\ W\\ &L_i = 0\ \mu H\\ &C_i = 5\ nF \end{split}$
	Pulse/frequency/switch output	$\begin{split} &U_i = DC\ 35\ V\\ &I_i = n.a.\\ &P_i = 1\ W\\ &L_i = 0\ \mu H\\ &C_i = 6\ nF \end{split}$
Option C	4-20mA HART	$\label{eq:Ui} \begin{split} &U_i = \text{DC 30 V} \\ &I_i = \text{n.a.} \\ &P_i = 1 \text{ W} \end{split}$

Order code for "Output"	Output type	Intrinsically safe values
	4-20mA analog	$L_i = 0 \mu H$ $C_i = 30 \text{ nF}$
Option D	4-20mA HART	$\begin{split} &U_i = DC~35~V\\ &I_i = n.a.\\ &P_i = 1~W\\ &L_i = 0~\mu H\\ &C_i = 5~nF \end{split}$
	Pulse/frequency/switch output	$\begin{split} &U_i = DC\ 35\ V\\ &I_i = n.a.\\ &P_i = 1\ W\\ &L_i = 0\ \mu H\\ &C_i = 6\ nF \end{split}$
	4 to 20 mA current input	$\begin{split} &U_i = DC\ 35\ V\\ &I_i = n.a.\\ &P_i = 1\ W\\ &L_i = 0\ \mu H\\ &C_i = 5\ nF \end{split}$
Option E	FOUNDATION Fieldbus	$\begin{array}{llllllllllllllllllllllllllllllllllll$
	Pulse/frequency/switch output	$\begin{split} &U_{i} = 35 \ V \\ &l_{i} = 300 \ mA \\ &P_{i} = 1 \ W \\ &L_{i} = 0 \ \mu H \\ &C_{i} = 6 \ nF \end{split}$
Option G	PROFIBUS PA	$\begin{array}{llllllllllllllllllllllllllllllllllll$
	Pulse/frequency/switch output	$\begin{split} &U_{i} = 35 \text{ V} \\ &l_{i} = 300 \text{ mA} \\ &P_{i} = 1 \text{ W} \\ &L_{i} = 0 \mu\text{H} \\ &C_{i} = 6 \text{ nF} \end{split}$

Type of protection IS

Order code for "Output"	Output type	Intrinsically safe values
Option A	4-20mA HART	$\begin{split} &U_{i} = DC \ 30 \ V \\ &I_{i} = 300 \ mA \\ &P_{i} = 1 \ W \\ &L_{i} = 0 \ \mu H \\ &C_{i} = 5 \ nF \end{split}$
Option B	4-20mA HART	$\begin{split} &U_{i} = DC \ 30 \ V \\ &I_{i} = 300 \ mA \\ &P_{i} = 1 \ W \\ &L_{i} = 0 \ \mu H \\ &C_{i} = 5 \ nF \end{split}$
	Pulse/frequency/switch output	$\begin{split} &U_{i} = DC \; 30 \; V \\ &I_{i} = 300 \; mA \\ &P_{i} = 1 \; W \\ &L_{i} = 0 \; \mu H \\ &C_{i} = 6 \; nF \end{split}$
Option C	4-20mA HART	U _i = DC 30 V I _i = 300 mA P _i = 1 W

Order code for "Output"	Output type	Intrinsically safe	values
	4-20mA analog	$L_i = 0 \mu H$ $C_i = 30 nF$	
Option D	4-20mA HART	$\begin{split} &U_i = \text{DC 30 V} \\ &I_i = 300 \text{ mA} \\ &P_i = 1 \text{ W} \\ &L_i = 0 \mu\text{H} \\ &C_i = 5 \text{ nF} \end{split}$	
	Pulse/frequency/switch output	$\begin{split} &U_i = DC~30~V\\ &I_i = 300~mA\\ &P_i = 1~W\\ &L_i = 0~\mu H\\ &C_i = 6~nF \end{split}$	
	4 to 20 mA current input	$\begin{split} &U_i = DC~30~V\\ &I_i = 300~mA\\ &P_i = 1~W\\ &L_i = 0~\mu H\\ &C_i = 5~nF \end{split}$	
Option E	FOUNDATION Fieldbus	$STANDARD \\ U_i = 30 \text{ V} \\ l_i = 300 \text{ mA} \\ P_i = 1.2 \text{ W} \\ L_i = 10 \mu\text{H} \\ C_i = 5 \text{ nF} \\ \\$	$FISCO \\ U_i = 17.5 \text{ V} \\ l_i = 550 \text{ mA} \\ P_i = 5.5 \text{ W} \\ L_i = 10 \mu\text{H} \\ C_i = 5 \text{ nF} \\ \\ \label{eq:definition}$
	Pulse/frequency/switch output	$\begin{split} U_i &= 30 \text{ V} \\ l_i &= 300 \text{ mA} \\ P_i &= 1 \text{ W} \\ L_i &= 0 \mu\text{H} \\ C_i &= 6 \text{ nF} \end{split}$	
Option G	PROFIBUS PA	$STANDARD \\ U_i = 30 \text{ V} \\ l_i = 300 \text{ mA} \\ P_i = 1.2 \text{ W} \\ L_i = 10 \mu\text{H} \\ C_i = 5 \text{ nF} \\ \\$	FISCO $ U_i = 17.5 \text{ V} $ $ l_i = 550 \text{ mA} $ $ P_i = 5.5 \text{ W} $ $ L_i = 10 \mu\text{H} $ $ C_i = 5 \text{ nF} $
	Pulse/frequency/switch output	$\begin{aligned} &U_{i} = 30 \text{ V} \\ &l_{i} = 300 \text{ mA} \\ &P_{i} = 1 \text{ W} \\ &L_{i} = 0 \mu\text{H} \\ &C_{i} = 6 \text{ nF} \end{aligned}$	

Low flow cut off

The switch points for low flow cut off are user-selectable.

Galvanic isolation

All outputs are galvanically isolated from one another.

Protocol-specific data

HART

Manufacturer ID	0x11
Device type ID	0x38
HART protocol revision	7
Device description files (DTM, DD)	Information and files under: www.endress.com
HART load	 Min. 250 Ω Max. 500 Ω

Dynamic variables	Read out the dynamic variables: HART command 3 The measured variables can be freely assigned to the dynamic variables.
	Measured variables for PV (primary dynamic variable) • Volume flow
	Corrected volume flow
	■ Mass flow
	Flow velocity
	TemperatureCalculated saturated steam pressure
	Steam quality
	■ Total mass flow
	■ Energy flow
	Heat flow difference
	Measured variables for SV, TV, QV (secondary, tertiary and quaternary
	dynamic variable) Volume flow
	Corrected volume flow
	 Mass flow
	Flow velocity
	■ Temperature
	Calculated saturated steam pressureSteam quality
	■ Total mass flow
	■ Energy flow
	Heat flow difference
	Condensate mass flow Described a purchase
	Reynolds numberTotalizer 1
	■ Totalizer 2
	■ Totalizer 3
	 HART input
	DensityPressure
	Specific volume
	Degree of overheating
Device variables	Read out the device variables: HART command 9 The device variables are permanently assigned.
	A maximum of 8 device variables can be transmitted:
	■ 0 = volume flow
	■ 1 = corrected volume flow
	• 2 = Mass flow
	3 = flow velocity4 = temperature
	 5 = calculated saturated steam pressure
	■ 6 = steam quality
	• 7 = total mass flow
	8 = energy flow9 = heat flow difference
	• 10 = condensate mass flow
	■ 11 = Reynolds number
	■ 12 = totalizer 1
	• 13 = totalizer 2
	14 = totalizer 315 = HART input
	■ 16 = density
	• 17 = pressure
	■ 18 = specific volume
	■ 19 = degree of overheating

FOUNDATION Fieldbus

Manufacturer ID	0x452B48
Ident number	0x1038
Device revision	1

18

DD revision	Information and files under:
CFF revision	www.endress.comwww.fieldbus.org
Device Tester Version (ITK version)	6.1.1
ITK Test Campaign Number	IT094200
Link Master capability (LAS)	Yes
Choice of "Link Master" and "Basic Device"	Yes Factory setting: Basic Device
Node address	Factory setting: 247 (0xF7)
Supported functions	The following methods are supported: Restart ENP Restart Diagnostic
Virtual Communication Relation	onships (VCRs)
Number of VCRs	44
Number of link objects in VFD	50
Permanent entries	1
Client VCRs	0
Server VCRs	10
Source VCRs	43
Sink VCRs	0
Subscriber VCRs	43
Publisher VCRs	43
Device Link Capabilities	
Slot time	4
Min. delay between PDU	8
Max. response delay	Min. 5

Transducer Blocks

Block	Contents	Output values
Setup Transducer Block (TRDSUP)	All parameters for standard commissioning.	No output values
Advanced Setup Transducer Block (TRDASUP)	All parameters for more accurate measurement configuration.	No output values
Display Transducer Block (TRDDISP)	Parameters for configuring the local display.	No output values
HistoROM Transducer Block (TRDHROM)	Parameters for using the HistoROM function.	No output values

Block	Contents	Output values
Diagnostic Transducer Block (TRDDIAG)	Diagnostics information.	Process variables (AI Channel) Temperature (7) Volume flow (9) Mass flow (11) Corrected volume flow (13) Flow velocity (37) Energy flow (38) Calculated saturated steam pressure (45) Total mass flow (46) Condensate mass flow (47) Steam quality (48) Heat flow difference (49) Reynolds number (50)
Expert Configuration Transducer Block (TRDEXP)	Parameters that require the user to have indepth knowledge of the operation of the device in order to configure the parameters appropriately.	No output values
Expert Information Transducer Block (TRDEXPIN)	Parameters that provide information about the state of the device.	No output values
Service Sensor Transducer Block (TRDSRVS)	Parameters that can only be accessed by Endress +Hauser Service.	No output values
Service Information Transducer Block (TRDSRVIF)	Parameters that provide Endress+Hauser Service with information about the state of the device.	No output values
Total Inventory Counter Transducer Block (TRDTIC)	Parameters for configuring all the totalizers and the inventory counter.	Process variables (AI Channel) Totalizer 1 (16) Totalizer 2 (17) Totalizer 3 (18)
Heartbeat Technology Transducer Block (TRDHBT)	Parameters for the configuration and comprehensive information about the results of the verification.	No output values
Heartbeat Results 1 Transducer Block (TRDHBTR1)	Information about the results of the verification.	No output values
Heartbeat Results 2 Transducer Block (TRDHBTR2)	Information about the results of the verification.	No output values
Heartbeat Results 3 Transducer Block (TRDHBTR3)	Information about the results of the verification.	No output values
Heartbeat Results 4 Transducer Block (TRDHBTR4)	Information about the results of the verification.	No output values

Function blocks

Block	Number of blocks	Contents	Process variables (Channel)
Resource Block (RB)	1	This Block (extended functionality) contains all the data that uniquely identify the device; it is the equivalent of an electronic nameplate for the device.	-
Analog Input Block (AI)	4	This Block (extended functionality) receives the measurement data provided by the Sensor Block (can be selected via a channel number) and makes the data available for other blocks at the output. Execution time: 13 ms	 Temperature (7) Mass flow (11) Volume flow (9) Corrected volume flow (13) Flow velocity (37) Energy flow (38) Calculated saturated steam pressure (45) Total mass flow (46) Condensate mass flow (47) Steam quality (48) Heat flow difference (49) Reynolds number (50)
Discrete Input Block (DI)	2	This Block (standard functionality) receives a discrete value (e.g. indicator that measuring range has been exceeded) and makes the value available for other blocks at the output. Execution time: 12 ms	 Switch output state (101) Low flow cut off (103) Status verification (105)
PID Block (PID)	1	This Block (standard functionality) acts as a proportional-integral-differential controller and can be used universally for control in the field. It enables cascading and feedforward control. Execution time: 13 ms	-
Multiple Analog Output Block (MAO)	1	This Block (standard functionality) receives several analog values and makes them available for other blocks at the output. Execution time: 11 ms	Channel_0 (121) Value 1: External compensation variable, pressure Value 2: External compensation variable, relative pressure Value 3: External compensation variable, density Value 4: External compensation variable, temperature Value 5: External compensation variable, second temperature heat difference Value 6 to 8: Not assigned The compensation variables must be transmitted to the device in the SI basic unit.

Block	Number of blocks	Contents	Process variables (Channel)
Multiple Digital Output Block (MDO)	1	This Block (standard functionality) receives several discrete values and makes them available for other blocks at the output. Execution time: 14 ms	Channel_DO (122) Value 1: Reset totalizer 1 Value 2: Reset totalizer 2 Value 3: Reset totalizer 3 Value 4: Flow override Value 5: Start heartbeat verification Value 6: Status switch output Value 7: Not assigned Value 8: Not assigned
Integrator Block (IT)	1	This Block (standard functionality) integrates a measured variable over time or totalizes the pulses from a Pulse Input Block. The Block can be used as a totalizer that totalizes until a reset, or as a batch totalizer whereby the integrated value is compared against a target value generated before or during the control routine and generates a binary signal when the target value is reached. Execution time: 16 ms	_

PROFIBUS PA

Manufacturer ID	0x11
Ident number	0x1564
Profile version	3.02
Device description files (GSD, DTM, DD)	Information and files under: www.endress.com www.profibus.org
Output values (from measuring device to automation system)	Analog input 1 to 4 Volume flow Mass flow Corrected volume flow Flow velocity Temperature Calculated saturated steam pressure Steam quality Total mass flow Energy flow Heat flow difference Reynolds number Density Pressure Specific volume Degree of overheating Digital input 1 to 2 Empty pipe detection Low flow cut off Status switch output Status verification Totalizer 1 to 3 Mass flow Volume flow Corrected volume flow Total mass flow Condensate mass flow Energy flow Heat flow difference


Input values (from automation system to measuring device)	Analog output ■ External density ■ External temperature Digital output 1 to 2 (fixed assignment) ■ Digital output 1: switch positive zero return on/off ■ Digital output 2: start verification
	Totalizer 1 to 3 Totalize Reset and hold Preset and hold Operating mode configuration: Net flow total Forward flow total Reverse flow total
Supported functions	 Identification & Maintenance Simplest device identification on the part of the control system and nameplate PROFIBUS upload/download Reading and writing parameters is up to ten times faster with PROFIBUS upload/download Condensed status Simplest and self-explanatory diagnostic information by categorizing diagnostic messages that occur
Configuration of the device address	 DIP switches on the I/O electronics module Local display via operating tools (e.g. FieldCare)

Power supply

Terminal assignment

Transmitter

Connection versions



- Output 2 (passive): supply voltage and signal transmission
- Input (passive): supply voltage and signal transmission
- Ground terminal for cable shield

Order code for "Output"	Terminal numbers						
	Outp	out 1	Outp	Output 2		Input	
	1 (+)	2 (-)	3 (+)	4 (-)	5 (+)	6 (-)	
Option A	4-20 mA HA	ART (passive)	-	-	-	-	
Option B ¹⁾	4-20 mA HART (passive)		Pulse/frequency/switch output (passive)		-		
Option C 1)	4-20 mA HART (passive)		4-20 mA ana	log (passive)	-		
Option D ^{1) 2)}	4-20 mA HART (passive)		Pulse/frequo output (,	4-20 mA cu (pas:		
Option E ^{1) 3)}	FOUNDATION Fieldbus		Pulse/frequo output (,	-		
Option G ^{1) 4)}	PROFIBUS PA		Pulse/frequo output (,	-		

- 1) Output 1 must always be used; output 2 is optional.
- 2) The integrated overvoltage protection is not used with option D: Terminals 5 and 6 (current input) are not protected against overvoltage.
- 3) FOUNDATION Fieldbus with integrated reverse polarity protection.
- 4) PROFIBUS PA with integrated reverse polarity protection.

Remote version

In the case of the remote version, the sensor and transmitter are mounted separately from one another and connected by a connecting cable. The sensor is connected via the connection housing while the transmitter is connected via the connection compartment of the wall holder unit.

The way the transmitter wall holder is connected depends on the measuring device approval

and the version of the connecting cable used.


Connection is only possible via terminals:

- For approvals Ex n, Ex tb and cCSAus Div. 1
- If a reinforced connecting cable is used

The connection is via an M12 connector:

- For all other approvals
- If the standard connecting cable is used

Connection to the connection housing of the sensor is always via the terminals (tightening torque for terminals: 1.2 to 1.7 Nm).



A001933

- 2 Terminals for connection compartment in the transmitter wall holder and the sensor connection housing
- 1 Terminals for connecting cable
- 2 Grounding via the cable strain relief

Terminal number	Assignment	Cable color Connecting cable
1	Supply voltage	Brown
2	Grounding	White

Terminal number	Assignment	Cable color Connecting cable
3	RS485 (+)	Yellow
4	RS485 (-)	Green

Pin assignment, device plug

PROFIBUS PA

Device plug for signal transmission (device side)

	Pin		Assignment	Coding	Plug/socket
	1	+	PROFIBUS PA +	A	Plug
1	2		Grounding		
A00190	3	-	PROFIBUS PA -		
	4		Not assigned		

FOUNDATION Fieldbus

Device plug for signal transmission (device side)

	Pin		Assignment	Coding	Plug/socket
$2 \longrightarrow 3$	1	+	Signal +	A	Plug
1 4	2	-	Signal –		
A001902:	3		Not assigned		
	4		Grounding		

Supply voltage

Transmitter

An external power supply is required for each output.

Supply voltage for a compact version without a local display $^{1)}$

Order code for "Output"	Minimum terminal voltage ²⁾	Maximum terminal voltage
Option A: 4-20 mA HART	≥ DC 12 V	DC 35 V
Option B : 4-20 mA HART, pulse/ frequency/switch output	≥ DC 12 V	DC 35 V
Option C : 4-20 mA HART + 4-20 mA analog	≥ DC 12 V	DC 30 V
Option D : 4-20 mA HART, pulse/ frequency/switch output, 4-20 mA current input ³⁾	≥ DC 12 V	DC 35 V
Option E: FOUNDATION Fieldbus, pulse/frequency/switch output	≥ DC 9 V	DC 32 V
Option G : PROFIBUS PA, pulse/frequency/switch output	≥ DC 9 V	DC 32 V

¹⁾ In event of external supply voltage of the power supply unit with load, the PROFIBUS DP/PA coupler or FOUNDATION Fieldbus power conditioner

²⁾ The minimum terminal voltage increases if local operation is used: see the following table

³⁾ Voltage drop 2.2 to 3 V for 3.59 to 22 mA

Increase in minimum terminal voltage

Local operation	Increase in minimum terminal voltage
Order code for "Display; Operation", option C : Local operation SD02	+ DC 1 V
Order code for "Display; Operation", option E: Local operation SD03 with lighting (backlighting not used)	+ DC 1 V
Order code for "Display; Operation", option E: Local operation SD03 with lighting (backlighting used)	+ DC 3 V

- Various power supply units can be ordered from Endress+Hauser: see "Accessories" section
 → 🖺 82
- For information on the Ex connection values $\rightarrow \triangleq 12$

Power consumption

Transmitter

Order code for "Output"	Maximum power consumption
Option A : 4-20 mA HART	770 mW
Option B : 4-20 mA HART, pulse/ frequency/switch output	 Operation with output 1: 770 mW Operation with output 1 and 2: 2770 mW
Option C : 4-20 mA HART + 4-20 mA analog	 Operation with output 1: 660 mW Operation with output 1 and 2: 1320 mW
Option D : 4-20 mA HART, pulse/ frequency/switch output, 4-20 mA current input	 Operation with output 1: 770 mW Operation with output 1 and 2: 2770 mW Operation with output 1 and input: 840 mW Operation with output 1, 2 and input: 2840 mW
Option E : FOUNDATION Fieldbus, pulse/frequency/switch output	 Operation with output 1: 512 mW Operation with output 1 and 2: 2512 mW
Option G : PROFIBUS PA, pulse/frequency/switch output	 Operation with output 1: 512 mW Operation with output 1 and 2: 2512 mW

Current consumption

Current output

For every 4-20 mA or 4-20 mA HART current output: 3.6 to 22.5 mA $\,$

If the option **Defined value** is selected in the **Failure mode** parameter: 3.59 to 22.5 mA

Current input

3.59 to 22.5 mA

Internal current limiting: max. 26 mA

PROFIBUS PA

15 mA

FOUNDATION Fieldbus


15 mA

Power supply failure

- Totalizers stop at the last value measured.
- Configuration is retained in the device memory (HistoROM).
- Error messages (incl. total operated hours) are stored.

Electrical connection


Connecting the transmitter



1 Cable entries for inputs/outputs

Remote version connection

Connecting cable



■ 3 Connecting cable connection

- 1 Wall holder with connection compartment (transmitter)
- 2 Connecting cable
- 3 Sensor connection housing

The way the transmitter wall holder is connected depends on the measuring device approval and the version of the connecting cable used.

Connection is only possible via terminals:

- For approvals Ex n, Ex tb and cCSAus Div. 1
- If a reinforced connecting cable is used


The connection is via an M12 connector:

- For all other approvals
- If the standard connecting cable is used

Connection to the connection housing of the sensor is always via the terminals (tightening torque for terminals: 1.2 to 1.7 Nm).


Connection examples

Current output 4-20 mA HART



- € 4 Connection example for 4-20 mA HART current output (passive)
- Automation system with current input (e.g. PLC) 1
- Active barrier for power supply with integrated resistor for HART communication ($\geq 250 \Omega$) (e.g. RN221N) Connection for HART operating devices $\rightarrow \Box$ 72 Observe the maximum load $\rightarrow \blacksquare 11$
- 3 Cable shield, observe cable specifications
- 4 Analog display unit: observe maximum load $\rightarrow = 11$
- Transmitter5


Pulse/frequency output



Connection example for pulse/frequency output (passive)


- Automation system with pulse/frequency input (e.g. PLC) 1
- 2 Power supply
- 3 *Transmitter: observe input values* $\rightarrow \bigcirc 9$

Switch output



- € 6 Connection example for switch output (passive)
- 1 Automation system with switch input (e.g. PLC)
- 2 Power supply
- 3 Transmitter: observe input values


PROFIBUS-PA



₽ 7 Connection example for PROFIBUS-PA

- Control system (e.g. PLC) Segment coupler PROFIBUS DP/PA 1 2 3
- Cable shield
- 4 5 T-box
- Measuring device
- 6 7 Local grounding Bus terminator
- Potential matching line


FOUNDATION Fieldbus



₽8 Connection example for FOUNDATION Fieldbus

- 1
- Control system (e.g. PLC) Power Conditioner (FOUNDATION Fieldbus)
- 3 Cable shield
- T-box
- 5 Measuring device
- 6 Local grounding
- Bus terminator 7
- 8 Potential matching line


Current input



9 Connection example for 4-20 mA current input

- Control system (e.g. PLC)
- 2 Power supply
- 3

HART input



A0016020

■ 10 Connection example for HART input with a common negative

- 1 Automation system with HART output (e.g. PLC)
- 2 Resistor for HART communication (\geq 250 Ω): observe maximum load \Rightarrow $\stackrel{\triangle}{=}$ 12
- 3 Active barrier for power supply (e.g. RN221N)
- 4 Cable shield, observe cable specifications
- 5 Analog display unit: observe maximum load → 🖺 12
- 6 Pressure transmitter (e.g. Cerabar M, Cerabar S): see requirements
- 7 Transmitter

Potential equalization

Requirements

Please consider the following to ensure correct measurement:

- Same electrical potential for the fluid and sensor
- Remote version: same electrical potential for the sensor and transmitter
- Company-internal grounding concepts
- Pipe material and grounding



For devices intended for use in hazardous locations, please observe the guidelines in the Ex documentation (XA).

Terminals

- For device version without integrated overvoltage protection: plug-in spring terminals for wire cross-sections 0.5 to 2.5 mm² (20 to 14 AWG)
- For device version with integrated overvoltage protection: screw terminals for wire cross-sections 0.2 to 2.5 mm² (24 to 14 AWG)

Cable entries

- Cable gland (not for Ex d): M20 \times 1.5 with cable ϕ 6 to 12 mm (0.24 to 0.47 in)
- Thread for cable entry:
 - For non-Ex and Ex: NPT ½"
 - For non-Ex and Ex (not for CSA Ex d/XP): G 1/2"
 - For Ex d: M20 × 1.5

Cable specification

Permitted temperature range

- -40 °C (-40 °F) to +80 °C (+176 °F)
- Minimum requirement: cable temperature range ≥ ambient temperature +20 K

Signal cable

Current output

- For 4-20 mA: standard installation cable is sufficient.
- For 4-20 mA HART: Shielded cable recommended. Observe grounding concept of the plant.

Pulse/frequency/switch output

Standard installation cable is sufficient.

Current input

Standard installation cable is sufficient.

FOUNDATION Fieldbus

Twisted, shielded two-wire cable.



For further information on planning and installing FOUNDATION Fieldbus networks see:

- Operating Instructions for "FOUNDATION Fieldbus Overview" (BA00013S)
- FOUNDATION Fieldbus Guideline
- IEC 61158-2 (MBP)

PROFIBUS PA

Twisted, shielded two-wire cable. Cable type A is recommended.



For further information on planning and installing PROFIBUS PA networks see:

- Operating Instructions "PROFIBUS DP/PA: Guidelines for planning and commissioning" (BA00034S)
- PNO Directive 2.092 "PROFIBUS PA User and Installation Guideline"
- IEC 61158-2 (MBP)

Connecting cable for remote version

Connecting cable (standard)

Standard cable	$2\times2\times0.34~\text{mm}^2$ (22 AWG) PVC cable with common shield (2 pairs, pair-stranded)
Flame resistance	According to DIN EN 60332-1-2
Oil-resistance	According to DIN EN 60811-2-1
Shielding	Galvanized copper-braid, opt. density approx. 85%
Cable length	5 m (16 ft), 10 m (32 ft), 20 m (65 ft), 30 m (98 ft)
Operating temperature	When mounted in a fixed position: -50 to $+105$ °C (-58 to $+221$ °F); when cable can move freely: -25 to $+105$ °C (-13 to $+221$ °F)

Connecting cable (reinforced)

Cable, reinforced	$2\times2\times0.34~mm^2$ (22 AWG) PVC cable with common shield (2 pairs, pair-stranded) and additional steel-wire braided sheath
Flame resistance	According to DIN EN 60332-1-2
Oil-resistance	According to DIN EN 60811-2-1
Shielding	Galvanized copper-braid, opt. density approx. 85%
Strain relief and reinforcement	Steel-wire braid, galvanized
Cable length	5 m (16 ft), 10 m (32 ft), 20 m (65 ft), 30 m (98 ft)
Operating temperature	When mounted in a fixed position: -50 to $+105$ °C (-58 to $+221$ °F); when cable can move freely: -25 to $+105$ °C (-13 to $+221$ °F)

Overvoltage protection

The device can be ordered with integrated overvoltage protection for diverse approvals: Order code for "Accessory mounted", option NA "Overvoltage protection"

Input voltage range	Values correspond to supply voltage specifications 1)
Resistance per channel	2 · 0.5 Ω max
DC sparkover voltage	400 to 700 V
Trip surge voltage	< 800 V
Capacitance at 1 MHz	< 1.5 pF

Nominal discharge current (8/20 μs)	10 kA	
Temperature range	−40 to +85 °C (−40 to +185 °F)	

The voltage is reduced by the amount of the internal resistance $I_{\text{min}}\cdotp R_i$ 1)

Depending on the temperature class, restrictions apply to the ambient temperature for device

Performance characteristics

Reference operating conditions

- Error limits following ISO/DIN 11631
- +20 to +30 °C (+68 to +86 °F)
- 2 to 4 bar (29 to 58 psi)
- Calibration system traceable to national standards
- Calibration with the process connection corresponding to the particular standard
- To obtain measured errors, use the *Applicator* sizing tool \rightarrow $\stackrel{\triangle}{=}$ 82


Maximum measured error

Base accuracy

o.r. = of reading, Re = Reynolds number

Volume flow

The measured error for the volume flow is as follows depending on the Reynolds number and the compressibility of the medium under measurement:



Deviat			
Medium type Incompressible			Compressible 1)
Re range Measured value deviation		Standard	Standard
R1 to R2	A2	< 10 %	< 10 %
R2 to Re _{max}	A1	< 0.75 %	< 1.0 %

Accuracy specifications valid up to 75 m/s (246 ft/s) 1)

Reynolds numbers	Incompressible	Compressible	
Reynolus numbers	Standard	Standard	
R1	5000		
R2	20 000		

Temperature

- Saturated steam and liquids at room temperature if T > 100 °C (212 °F) applies: < 1 °C (1.8 °F)
- Gas: < 1 % o.r. [K]
- Volume flow: > 70 m/s (230 ft/s): 2% o.r.

Rise time 50 % (stirred under water, following IEC 60751): 8 s

Mass flow (saturated steam)

- Flow velocities 20 to 50 m/s (66 to 164 ft/s), T > 150 °C (302 °F) or (423 K)
 - Re > 20000: < 1.7 % o.r.
 - Re between 5000 to 20000: < 10 % o.r.
- Flow velocities 10 to 70 m/s (33 to 210 ft/s), T > 140 °C (284 °F) or (413 K)
 - Re > 20000: < 2 % o.r.
 - Re between 5 000 to 20 000: < 10 % o.r.
- Flow velocities < 10 m/s (33 ft/s): Re > 5000: 5%
- The use of a Cerabar S is required for the measured errors listed in the following section. The measured error used to calculate the error in the measured pressure is 0.15%.

Mass flow of superheated steam and gas (single gas, gas mixture, air: NEL40; natural gas: ISO 12213-2 contains AGA8-DC92, AGA NX-19, ISO 12213-3 contains SGERG-88 and AGA8 Gross Method 1)

- Re > 20000 and process pressure < 40 bar abs. (580 psi abs.): 1.7 % o.r.
- Re between 5 000 to 20 000 and process pressure < 40 bar abs. (580 psi abs.): 10 % o.r.
- Re > 20000 and process pressure < 120 bar abs. (1740 psi abs.): 2.6 % o.r.
- Re between 5000 to 20000 and process pressure < 120 bar abs. (1740 psi abs.): 10 % o.r.

abs. = absolute

Mass flow (water)

- Re 20000: < 0.85 % o.r.
- Re between 5000 to 20000: < 10 % o.r.

Mass flow (user-defined liquids)

To specify the system accuracy, Endress+Hauser requires information about the type of liquid and its operating temperature or information in table form about the dependency between the liquid density and the temperature.

Example

- Acetone is to be measured at fluid temperatures from +70 to +90 °C (+158 to +194 °F).
- For this purpose, the **Reference temperature** parameter (7703) (here 80 °C (176 °F)), **Reference density** parameter (7700) (here 720.00 kg/m³) and **Linear expansion coefficient** parameter (7621) (here 18.0298 × 10⁻⁴ 1/°C) must be entered in the transmitter.
- The overall system uncertainty, which is less than 0.9 % for the example above, is comprised of the following measurement uncertainties: uncertainty of volume flow measurement, uncertainty of temperature measurement, uncertainty of the density-temperature correlation used (incl. the resulting uncertainty of density).

Mass flow (other media)

Depends on the selected fluid and the pressure value, which is specified in the parameters. Individual error analysis must be performed.

Diameter mismatch correction

Prowirl 200 can correct shifts in the calibration factor which are caused, for example, by diameter mismatch between the device flange (e.g. ASME B16.5/Sch. 80, DN 50 (2")) and the mating pipe (e.g. ASME B16.5/Sch. 40, DN 50 (2")). Only apply diameter mismatch correction within the following limit values (listed below) for which test measurements have also been performed.

Disc (wafer flange):


- DN 15 ($\frac{1}{2}$ "): ±15 % of the internal diameter
- DN 25 (1"): ±12 % of the internal diameter
- DN 40 (1½"): ± 9 % of the internal diameter
- DN \geq 50 (2"): \pm 8 % of the internal diameter

If the standard internal diameter of the ordered process connection differs from the internal diameter of the mating pipe, an additional measuring uncertainty of approx. $2\,\%$ o.r. must be expected.

Example

Influence of the diameter mismatch without using the correction function:

- Mating pipe DN 100 (4"), schedule 80
- Device flange DN 100 (4"), schedule 40
- This installation position results in a diameter mismatch of 5 mm (0.2 in). If the correction function is not used, an additional measuring uncertainty of approx. 2 % o.r. must be expected.



Accuracy of outputs

The outputs have the following base accuracy specifications.

Current output

A cours ou	I ±10Λ
Accuracy	±10 μA
,	!

Pulse/frequency output

o.r. = of reading

Accura	ıcy	Max. ±100 ppm o.r.
--------	-----	--------------------

Repeatability

o.r. = of reading

±0.2 % o.r.

Response time

If all the configurable functions for filter times (flow damping, display damping, current output time constant, frequency output time constant, status output time constant) are set to 0, in the event of vortex frequencies of 10 Hz and higher a response time of $max(T_v, 100 \text{ ms})$ can be expected.

In the event of measuring frequencies < 10 Hz, the response time is > 100 ms and can be up to 10 s. T_v is the average vortex period duration of the flowing fluid.

Influence of ambient temperature

Current output

o.r. = of reading

Additional error, based on span of 16 mA:

Temperature coefficient at zero point (4 mA)	0.02 %/10 K
Temperature coefficient with span (20 mA)	0.05 %/10 K


Pulse/frequency output

o.r. = of reading

Temperature coefficient	Max. ±100 ppm o.r.
1	r r

Installation

Mounting location



A0015543

Orientation


The direction of the arrow on the sensor nameplate helps you to install the sensor according to the flow direction (direction of medium flow through the piping).

Vortex meters require a fully developed flow profile as a prerequisite for correct volume flow measurement. Therefore, please note the following:

	Orientation	Compact version	Remote version	
A	Vertical orientation	A0015545	VV 1)	VV
В	Horizontal orientation, transmitter head up	A0015589	νν ²⁾³⁾	VV
С	Horizontal orientation, transmitter head down	A0015590	√ √ ^{4) 5)}	VV
D	Horizontal orientation, transmitter head at side	A0015592	∨∨ ⁴⁾	VV

- In the case of liquids, there should be upward flow in vertical pipes to avoid partial pipe filling (Fig. A).
 Disruption in flow measurement! In the case of vertical orientation and downward flowing liquid, the pipe always needs to be completely filled to ensure correct liquid flow measurement.
- Danger of electronics overheating! If the fluid temperature is \geq 200 °C (392 °F) orientation B is not permitted for the wafer version (Prowirl D) with nominal diameters DN 100 (4") and DN 150 (6").
- 3) In the case of hot media (e.g. steam or fluid temperature (TM) \geq 200 °C (392 °F): orientation C or D
- 4) In the case of very cold media (e.g. liquid nitrogen): orientation B or D
- 5) For "wet steam detection/measurement" option: orientation C

Minimum spacing and cable length



- A Minimum spacing in all directions
- L Required cable length

The following dimensions must be observed to guarantee problem-free access to the device for service purposes:


- \bullet A = 100 mm (3.94 in)
- L = L + 150 mm (5.91 in)

Rotating the electronics housing and the display

The electronics housing can be rotated continuously by 360 $^{\circ}$ on the housing support. The display unit can be rotated in 45 $^{\circ}$ stages. This means you can read the display comfortably from all directions.

Inlet and outlet runs

To attain the specified level of accuracy of the measuring device, the inlet and outlet runs mentioned below must be maintained at the very minimum.



A00191

■ 11 Minimum inlet and outlet runs with various flow obstructions


- h Difference in expansion
- 1 Reduction by one nominal diameter size
- 2 Single elbow (90° elbow)
- 3 Double elbow (2 × 90° elbows, opposite)
- 4 Double elbow 3D ($2 \times 90^{\circ}$ elbows, opposite, not on one plane)
- 5 T-piece
- 6 Expansion
- 7 Control valve
- 8 Two measuring devices in a row where DN \leq 25 (1"): directly flange on flange
- 9 Two measuring devices in a row where DN ≥ 40 (1½"): for spacing, see graphic



- If there are several flow disturbances present, the longest specified inlet run must be maintained.

Flow conditioner

If the required inlet runs cannot be observed, it is possible to install a specially designed flow conditioner which can be ordered from Endress+Hauser. The flow conditioner is fitted between two pipe flanges and centered by the mounting bolts. Generally this reduces the inlet run needed to $10 \times DN$ with full accuracy.



Flow conditioner

The pressure loss for flow conditioners is calculated as follows: $\Delta p \text{ [mbar]} = 0.0085 \cdot \rho \text{ [kg/m}^3] \cdot v^2$ [m/s]

Example for steam

p = 10 bar abs.

 $t = 240 \, ^{\circ}\text{C} \rightarrow \rho = 4.39 \, \text{kg/m}^3$

v = 40 m/s

 $\Delta p = 0.0085 \cdot 4.394.39 \cdot 40^{2} = 59.7 \text{ mbar}$

Example for H₂O condensate (80 °C)

 $\rho = 965 \text{ kg/m}^3$

v = 2.5 m/s

 $\Delta p = 0.0085 \cdot 965 \cdot 2.5^2 = 51.3 \text{ mbar}$

 $\boldsymbol{\rho}$: density of the process medium


v: average flow velocity

abs. = absolute

For information on the flow conditioner

Outlet runs when installing external devices

If installing an external device, observe the specified distance.



PT Pressure transmitter

Temperature transmitter


Mounting kit

Mounting kit for disc (wafer version)

The centering rings supplied are used to mount and center the wafer-style devices.

A mounting kit comprises:

- Tie rods
- Seals
- Nuts
- Washers



■ 12 Mounting kit for wafer version

- Nut, washer, tie rod
- Seal
- *Centering ring (is supplied with the measuring device)*


Length of connecting cable

To ensure correct measuring results when using the remote version,

- observe the maximum permitted cable length: L_{max} = 30 m (90 ft). The value for the cable length must be calculated if the cable cross-section differs from the specification.
 - For detailed information about calculating the length of the connecting cable, refer to the Operating Instructions for the device on the CD-ROM provided


Installing the wall-mount housing

Wall mounting



■ 13 Engineering unit mm (in)

Post mounting



🖪 14 🛮 Engineering unit mm (in)

1 Post retainer kit for post mounting


Special mounting instructions

Installation for delta heat measurements

Order code for "Sensor version", option 3 "Mass flow (integrated temperature measurement)"

The second temperature measurement is taken using a separate temperature sensor. The measuring device reads in this value via a communication interface.

- In the case of saturated steam delta heat measurements, the Prowirl 200 must be installed on the steam side.
- In the case of water delta heat measurements, the Prowirl 200 can be installed on the cold or warm side.



 $label{eq:local_state}
label{eq:local_state} 15$ Layout for delta heat measurement of saturated steam and water

- 1 Prowir
- 2 Temperature sensor
- 3 Heat exchanger
- Q Heat flow

Weather protection cover

Observe the following minimum head clearance: 222 mm (8.74 in)



Environment

Ambient temperature range

Compact version

Measuring device	Non-Ex:	-40 to +80 °C (-40 to +176 °F) ¹⁾
	Ex i:	-40 to +70 °C (-40 to +158 °F) 1)
	EEx d/XP version:	-40 to +60 °C (-40 to +140 °F) 1)
	ATEX II1/2G Ex d, Ex ia:	-40 to +60 °C (-40 to +140 °F) 1)
Local display		-20 to +70 °C (-4 to +158 °F) ¹⁾

1) Additionally available as order code for "Test, certificate", option JN "Transmitter ambient temperature -50 °C (-58 °F)".

Remote version

Transmitter	Non-Ex:	-40 to +80 °C (-40 to +176 °F) ¹⁾	
	Ex i:	-40 to +80 °C (-40 to +176 °F) ¹⁾	
	Ex d:	-40 to +60 °C (-40 to +140 °F) 1)	
	ATEX II1/2G Ex d, Ex ia:	-40 to +60 °C (-40 to +140 °F) ¹⁾	
Sensor	Non-Ex:	-40 to +85 °C (-40 to +185 °F) ¹⁾	
	Ex i:	-40 to +85 °C (-40 to +185 °F) ¹⁾	
	Ex d:	-40 to +85 °C (-40 to +185 °F) ¹⁾	
	ATEX II1/2G Ex d, Ex ia:	-40 to +85 °C (-40 to +185 °F) ¹⁾	
Local display		-20 to +70 °C (-4 to +158 °F) ¹⁾	

- 1) Additionally available as order code for "Test, certificate", option JN "Transmitter ambient temperature -50 °C (-58 °F)".
- ► If operating outdoors:

Avoid direct sunlight, particularly in warm climatic regions.

Weather protection covers can be ordered from Endress+Hauser: see "Accessories" section $\rightarrow \stackrel{ riangle}{=} 80$

Temperature tables

 $T_{\rm m}$ = fluid temperature, $T_{\rm a}$ = ambient temperature

The following interdependencies between the permitted ambient and fluid temperatures apply when operating the device in hazardous areas:

Compact version

Order code for "Sensor version", option 1 "Volume flow, basis"; option 3 "Mass flow (integrated temperature measurement)"

Order code for "Sensor version", option 2 "Volume flow, high-temperature/low-temperature"

The following temperature tables apply to the low-temperature version $\rightarrow \triangleq 43$.

42

Order code for "Output", option A "4-20mA HART"

Order code for "Approval", all options

- Ex d, Ex ia, Ex ic, Ex nA, Ex tb
- CCSA_{US} IS, CCSA_{US} XP, CCSA_{US} NI

SI units

Version v	Version with max. $T_m = 280 ^{\circ}\text{C}$								
T _a 1) [°C]	T6 [85 °C]	T5 [100°C]	T4 [135 ℃]	T3 [200 ℃]	T2 [300 °C]	T1 [450 ℃]			
40	80	95	130	195	280	-			
60	-	95	130	195	280	-			
65	-	-	130	195	280	-			
70	-	_	130	-	-	_			

1) The following applies for installations with overvoltage protection in conjunction with temperature class T5, T6 and approval options BA, BB, BD, BH, BJ, B2, IA, IB, ID, IH, IJ, I4, C2: $T_a = T_a - 2 \,^{\circ}C$

US units

Version v	Version with max. $T_m = 536 ^{\circ}F$								
T _a 1) [°F]	T6 [185 °F]	T5 [212 °F]	T4 [275 °F]	T3 [392 °F]	T2 [572 °F]	T1 [842 °F]			
104	176	203	266	383	536	-			
140	-	203	266	383	536	-			
149	-	-	266	383	536	-			
158	-	-	266	_	-	-			

The following applies to installations with overvoltage protection in conjunction with temperature class T5, T6 and approval options BA, BB, BD, BH, BJ, B2, IA, IB, ID, IH, IJ, I4, C2: $T_a = T_a - 35.6$ °F

Order code for "Output", option B "4-20mA HART, pulse/frequency/switch output"

Order code for "Approval", options BA, BB, BD, BH, BJ, B2, IA, IB, ID, IH, IJ, I4, C2

- Ex ia, Ex ic, Ex tb
- $\, \bullet \,\,_{C}CSA_{US}$ IS

SI units

Version w	Version with max. $T_m = 280 ^{\circ}\text{C}$								
T _a 1) [°C]	T6 [85 ℃]	T5 [100 °C]	T4 [135 ℃]	T3 [200 °C]	T2 [300 °C]	T1 [450 ℃]			
35 ²⁾	80	95	130	195	280	-			
50 ³⁾	_	95	130	195	280	_			
60	_	_	130	195	280	_			
65	-	_	130	195	280 4)	_			
70	_	_	130	195 ⁵⁾	280 ⁵⁾	_			

- 1) The following applies for installations with overvoltage protection in conjunction with temperature class T5, T6 and approval options BA, BB, BD, BH, BJ, B2, IA, IB, ID, IH, IJ, I4, C2: $T_a = T_a 2$ °C
- T_a = 40 °C for pulse/frequency/switch output P_i = 0.85 W
- 3) $T_a = 55$ °C for pulse/frequency/switch output $P_i = 0.85$ W
- 4) $T_a = 65$ °C for pulse/frequency/switch output $P_i = 0.7$ W
- 5) $T_a = 70$ °C for pulse/frequency/switch output $P_i = 0.7$ W

US units

Version with max. $T_m = 536 ^{\circ}F$									
T _a ¹⁾ [°F]	T6 [185 °F]	T5 [212 °F]	T4 [275 °F]	T3 [392 °F]	T2 [572 °F]	T1 [842 °F]			
95 ²⁾	176	203	266	383	536	-			
122 ³⁾	_	203	266	383	536	_			
140	_	_	266	383	536	_			
149	_	_	266	383	536 ⁴⁾	_			
158	_	_	266	383 ⁵⁾	536 ⁵⁾	_			

- 1) The following applies to installations with overvoltage protection in conjunction with temperature class T5, T6 and approval options BA, BB, BD, BH, BJ, B2, IA, IB, ID, IH, IJ, I4, C2: $T_a = T_a 35.6$ °F
- 2) $T_a = 104$ °F for pulse/frequency/switch output $P_i = 0.85$ W
- 3) $T_a = 131$ °F for pulse/frequency/switch output $P_i = 0.85$ W
- 4) $T_a = 149$ °F for pulse/frequency/switch output $P_i = 0.7$ W
- T_a = 158 °F for pulse/frequency/switch output P_i = 0.7 W

Order code for "Approval", options BC, BG, BK, B3, IC, IG, IK, I5, C3

- Ex d, Ex nA, Ex tb
- CCSA_{US} XP

SI units

Version	Version with max. $T_m = 280 ^{\circ}\text{C}$								
T _a [°C]	T6 [85 °C]	T5 [100 ℃]	T4 [135 ℃]	T3 [200 ℃]	T2 [300 °C]	T1 [450 ℃]			
40	80	95	130	195	280	-			
55	-	95	130	195	280	-			
65	-	-	130	195	280 ¹⁾	-			
70	-	-	130	195 ²⁾	280 ²⁾	-			

- 1) $T_a = 65$ °C for pulse/frequency/switch output $P_i = 0.7$ W
- 2) $T_a = 70$ °C for pulse/frequency/switch output $P_i = 0.7$ W

US units

Version	Version with max. $T_m = 536 ^{\circ}F$								
T _a [°F]	T6 [185 °F]	T5 [212 °F]	T4 [275 °F]	T3 [392 °F]	T2 [572 °F]	T1 [842 °F]			
104	176	203	266	383	536	_			
131	-	203	266	383	536	-			
149	-	-	266	383	536 ¹⁾	-			
158	_	_	266	383 ²⁾	536 ²⁾	_			

- 1) $T_a = 149$ °F for pulse/frequency/switch output $P_i = 0.7$ W
- 2) $T_a = 158$ °F for pulse/frequency/switch output $P_i = 0.7$ W

Order code for "Output", option C "4-20mA HART, 4-20mA analog"

Order code for "Approval", all options

- Ex d, Ex ia, Ex ic, Ex nA, Ex tb
- CCSA_{US} IS, CCSA_{US} XP, CCSA_{US} NI

SI units

Version v	Version with max. $T_m = 280 ^{\circ}\text{C}$								
T _a 1) [°C]	T6 [85 °C]	T5 [100°C]	T4 [135 ℃]	T3 [200 ℃]	T2 [300 °C]	T1 [450°C]			
40	80	95	130	195	280	_			
55	_	95	130	195	280	-			
60	_	_	130	195	280	_			
65	_	_	130	195	280 ²⁾	_			
70	_	_	130	_	_	-			

- The following applies for installations with overvoltage protection in conjunction with temperature class T5, T6 and approval options BA, BB, BD, BH, BJ, B2, IA, IB, ID, IH, IJ, I4, C2: $T_a = T_a 2$ °C
- 2) $T_a = 65$ °C for pulse/frequency/switch output $P_i = 0$ W

US units

Version v	Version with max. T_m = 536 $^{\circ}F$								
T _a 1) [°F]	T6 [185 °F]	T5 [212 °F]	T4 [275 °F]	T3 [392 °F]	T2 [572 °F]	T1 [842 °F]			
104	176	203	266	383	536	-			
131	_	203	266	383	536	-			
140	_	_	266	383	536	-			
149	_	_	266	383	536 ²⁾	_			
158	-	-	266	-	-	-			

- 1) The following applies to installations with overvoltage protection in conjunction with temperature class T5, T6 and approval options BA, BB, BD, BH, BJ, B2, IA, IB, ID, IH, IJ, I4, C2: $T_a = T_a 35.6$ °F
- 2) $T_a = 149$ °F for pulse/frequency/switch output $P_i = 0$ W

Order code for "Output", option D "4-20 mA HART, PFS output; 4-20 mA input"

Order code for "Approval", all options

- Ex d, Ex ia, Ex ic, Ex nA, Ex tb
- ullet CCSA_{US} IS, CCSA_{US} XP, CCSA_{US} NI

SI units

Version v	Version with max. $T_m = 280$ °C								
T _a 1) [°C]	T6 [85 °C]	T5 [100 °C]	T4 [135 ℃]	T3 [200 °C]	T2 [300 °C]	T1 [450 ℃]			
35	80	95	130	195	280	-			
50	-	95	130	195	280	-			
55	-	-	-	195	280	-			
60	-	-	-	195	-	_			

The following applies for installations with overvoltage protection in conjunction with temperature class T5, T6 and approval options BA, BB, BD, BH, BJ, B2, IA, IB, ID, IH, IJ, I4, C2: $T_a = T_a - 2$ °C

US units

Version v	Version with max. $T_m = 536 ^{\circ}F$								
T _a 1) [°F]	T6 [185 °F]	T5 [212 °F]	T4 [275 °F]	T3 [392 °F]	T2 [572 °F]	T1 [842 °F]			
95	176	203	266	383	536	-			
122	-	203	266	383	536	-			
131	-	_	-	383	536	-			
140	-	_	-	383	-	-			

The following applies to installations with overvoltage protection in conjunction with temperature class T5, T6 and approval options BA, BB, BD, BH, BJ, B2, IA, IB, ID, IH, IJ, I4, C2: $T_a = T_a - 35.6$ °F

Order code for "Output", option E "FOUNDATION Fieldbus, pulse/frequency/switch output" and option G "PROFIBUS PA, pulse/frequency/switch output"

Order code for "Approval", all options

- Ex d, Ex ia, Ex ic, Ex nA, Ex tb
- lacktriangledown CCSA $_{US}$ IS, $_{C}$ CSA $_{US}$ XP, $_{C}$ CSA $_{US}$ NI

SI units

Version w	Version with max. $T_m = 280 ^{\circ}\text{C}$								
T _a 1) [°C]	T6 [85 °C]	T5 [100 °C]	T4 [135 ℃]	T3 [200 °C]	T2 [300 °C]	T1 [450 ℃]			
40	80	95	130	195	280	-			
50 ²⁾	-	95	130	195	280	_			
60	_	-	130	195	280	_			
65	_	-	130	195	280 ³⁾	_			
70	_	_	130	195 ⁴⁾	280 ⁴⁾	_			

- The following applies for installations with overvoltage protection in conjunction with temperature class T5, T6 and approval options BA, BB, BD, BH, BJ, B2, IA, IB, ID, IH, IJ, I4, C2: $T_a = T_a 2$ °C
- 2) $T_a = 60$ °C for pulse/frequency/switch output $P_i = 0$ W
- 3) $T_a = 65$ °C for pulse/frequency/switch output $P_i = 0$ W
- 4) $T_a = 70$ °C for pulse/frequency/switch output $P_i = 0$ W

US units

Version wit	Version with max. $T_m = 536 ^{\circ}F$									
T _a ¹⁾ [°F]	T6 [185 °F]	T5 [212 °F]	T4 [275 °F]	T3 [392 °F]	T2 [572 °F]	T1 [842 °F]				
104	176	203	266	383	536	-				
122 ²⁾	_	203	266	383	536	-				
140	_	_	266	383	536	-				
149	_	_	266	383	536 ³⁾	-				
158	_	_	266	383 ⁴⁾	536 ⁴⁾	_				

- The following applies to installations with overvoltage protection in conjunction with temperature class T5, T6 and approval options BA, BB, BD, BH, BJ, B2, IA, IB, ID, IH, IJ, I4, C2: $T_a = T_a 35.6$ °F
- 2) $T_a = 140$ °F for pulse/frequency/switch output $P_i = 0$ W
- 3) $T_a = 149$ °F for pulse/frequency/switch output $P_i = 0$ W
- 4) $T_a = 158$ °F for pulse/frequency/switch output $P_i = 0$ W

High-temperature version

Order code for "Sensor version", option 2 "Volume flow, high-temperature/low-temperature"

Order code for "Output", option A "4-20mA HART"

Order code for "Approval", all options

- Ex d, Ex ia, Ex ic, Ex nA, Ex tb
- CCSA_{US} IS, CCSA_{US} XP, CCSA_{US} NI

SI units

Version with max. T_m = 440 °C									
T _a 1) [°C]	T6 [85 ℃]	T5 [100°C]	T4 [135 ℃]	T3 [200 ℃]	T2 [300 °C]	T1 [450 ℃]			
40	80	95	130	195	290	440			
60	_	95	130	195	290	440			
70	-	-	130	195	290	440			

The following applies for installations with overvoltage protection in conjunction with temperature class T5, T6 and approval options BA, BB, BD, BH, BJ, B2, IA, IB, ID, IH, IJ, I4, C2: $T_a = T_a - 2$ °C

US units

Version with max. T_m = 824 °F								
T _a 1) [°F]	T6 [185 °F]	T5 [212 °F]	T4 [275 °F]	T3 [392 °F]	T2 [572 °F]	T1 [842 °F]		
104	176	203	266	383	554	824		
140	-	203	266	383	554	824		
158	-	-	266	383	554	824		

1) The following applies to installations with overvoltage protection in conjunction with temperature class T5, T6 and approval options BA, BB, BD, BH, BJ, B2, IA, IB, ID, IH, IJ, I4, C2: $T_a = T_a - 35.6$ °F

Order code for "Output", option B "4-20mA HART, pulse/frequency/switch output"

Order code for "Approval", options BA, BB, BD, BH, BJ, B2, IA, IB, ID, IH, IJ, I4, C2

- Ex ia, Ex ic, Ex tb
- ${lue}_{C}CSA_{US}$ IS

SI units

Version with max. T_m = 440 °C									
T _a 1) [°C]	T6 [85 ℃]	T5 [100°C]	T4 [135 ℃]	T3 [200 ℃]	T2 [300 °C]	T1 [450 ℃]			
35 ²⁾	80	95	130	195	290	440			
50 ³⁾	-	95	130	195	290	440			
65	-	-	130	195	290	440			
70	_	-	130	195 ⁴⁾	290	440 ⁴⁾			

- The following applies for installations with overvoltage protection in conjunction with temperature class 1) T5, T6 and approval options BA, BB, BD, BH, BJ, B2, IA, IB, ID, IH, IJ, I4, C2: $T_a = T_a - 2$ °C
- $T_a = 40$ °C for pulse/frequency/switch output $P_i = 0.85$ W
- 3) $T_a = 55$ °C for pulse/frequency/switch output $P_i = 0.85$ W
- $T_a = 70$ °C for pulse/frequency/switch output $P_i = 0.85$ W

US units

Version with max. T_m = 824 °F									
T _a 1) [°F]	T6 [185 °F]	T5 [212 °F]	T4 [275 °F]	T3 [392 °F]	T2 [572 °F]	T1 [842 °F]			
95 ²⁾	176	203	266	383	554	824			
122 ³⁾	_	203	266	383	554	824			
149	-	-	266	383	554	824			
158	-	-	266	383 ⁴⁾	554	824 4)			

- The following applies to installations with overvoltage protection in conjunction with temperature class T5, T6 and approval options BA, BB, BD, BH, BJ, B2, IA, IB, ID, IH, IJ, I4, C2: $T_a = T_a 35.6 \,^{\circ}F$
- 2) $T_a = 104$ °F for pulse/frequency/switch output $P_i = 0.85$ W
- 3) $T_a = 131$ °F for pulse/frequency/switch output $P_i = 0.85$ W
- 4) $T_a = 158$ °F for pulse/frequency/switch output $P_i = 0.85$ W

Order code for "Approval", options BC, BG, BK, B3, IC, IG, IK, I5, C3

- Ex d, Ex nA, Ex tb
- CCSAUS XP

SI units

Version with max. T_m = 440 °C									
T _a [°C]	T6 [85 °C]	T5 [100°C]	T4 [135 ℃]	T3 [200 °C]	T2 [300°C]	T1 [450 ℃]			
40	80	95	130	195	290	440			
55	-	95	130	195	290	440			
65	-	-	130	195	290	440			
70	-	-	130	195 ¹⁾	290 ¹⁾	440 ¹⁾			

1) $T_a = 70$ °C for pulse/frequency/switch output $P_i = 0.85$ W

US units

Version	Version with max. T_m = 824 $^{\circ}F$									
T _a [°F]	T6 [185 °F]	T5 [212 °F]	T4 [275 °F]	T3 [392 °F]	T2 [572 °F]	T1 [842 °F]				
104	176	203	266	383	554	824				
131	_	203	266	383	554	824				
149	-	-	266	383	554	824				
158	-	-	266	383 ¹⁾	554 ¹⁾	824 1)				

1) $T_a = 158$ °F for pulse/frequency/switch output $P_i = 0.85$ W

Order code for "Output", option C "4-20mA HART, 4-20mA analog"

Order code for "Approval", all options

- Ex d, Ex ia, Ex ic, Ex nA, Ex tb
- CCSA_{US} IS, CCSA_{US} XP, CCSA_{US} NI

SI units

Version with max. T_m = 440 °C									
T _a 1) [°C]	T6 [85 ℃]	T5 [100 ℃]	T4 [135 ℃]	T3 [200 ℃]	T2 [300 °C]	T1 [450 ℃]			
40	80	95	130	195	290	440			
55	-	95	130	195	290	440			
65	-	-	130	195	290	440			
70	-	-	130	195 ²⁾	290 ²⁾	440 ²⁾			

- 1) The following applies for installations with overvoltage protection in conjunction with temperature class T5, T6 and approval options BA, BB, BD, BH, BJ, B2, IA, IB, ID, IH, IJ, I4, C2: $T_a = T_a 2$ °C
- 2) $T_a = 70$ °C for pulse/frequency/switch output $P_i = 0$ W

US units

Version with max. T_m = 824 $^{\circ}F$									
T _a 1) [°F]	T6 [185 °F]	T5 [212 °F]	T4 [275 °F]	T3 [392 °F]	T2 [572 °F]	T1 [842 °F]			
104	176	203	266	383	554	824			
131	-	203	266	383	554	824			
149	-	-	266	383	554	824			
158	-	-	266	383 ²⁾	554 ²⁾	824 ²⁾			

- The following applies to installations with overvoltage protection in conjunction with temperature class T5, T6 and approval options BA, BB, BD, BH, BJ, B2, IA, IB, ID, IH, IJ, I4, C2: $T_a = T_a 35.6$ °F
- 2) $T_a = 158$ °F for pulse/frequency/switch output $P_i = 0$ W

Order code for "Output", option D "4-20 mA HART, PFS output; 4-20 mA input" Order code for "Approval", all options

- Ex d, Ex ia, Ex ic, Ex nA, Ex tb
- CCSA_{US} IS, CCSA_{US} XP, CCSA_{US} NI

SI units

Version with max. T_m = 440 °C									
T _a 1) [°C]	T6 [85 °C]	T5 [100 ℃]	T4 [135 ℃]	T3 [200 ℃]	T2 [300 °C]	T1 [450 ℃]			
35	80	95	130	195	290	440			
50	-	95	130	195	290	440			
55	-	-	-	195	290	440			
60	-	-	-	195	290	440			
65	-	-	-	-	290	-			

1) The following applies for installations with overvoltage protection in conjunction with temperature class T5, T6 and approval options BA, BB, BD, BH, BJ, B2, IA, IB, ID, IH, IJ, I4, C2: $T_a = T_a - 2$ °C

US units

Version with max. T_m = 824 $^{\circ}F$								
T _a 1) [°F]	T6 [185 °F]	T5 [212 °F]	T4 [275 °F]	T3 [392 °F]	T2 [572 °F]	T1 [842 °F]		
95	176	203	266	383	554	824		
122	-	203	266	383	554	824		

Version with max. T_m = 824 $^{\circ}F$									
T _a 1) [°F]	T6 [185 °F]	T5 [212 °F]	T4 [275 °F]	T3 [392 °F]	T2 [572 °F]	T1 [842 °F]			
131	-	-	-	383	554	824			
140	-	-	-	383	554	824			
149	_	_	_	_	554	_			

The following applies to installations with overvoltage protection in conjunction with temperature class T5, T6 and approval options BA, BB, BD, BH, BJ, B2, IA, IB, ID, IH, IJ, I4, C2: $T_a = T_a - 35.6$ °F

Order code for "Output", option E "FOUNDATION Fieldbus, pulse/frequency/switch output" and option G "PROFIBUS PA, pulse/frequency/switch output" $\frac{1}{2}$

Order code for "Approval", all options

- Ex d, Ex ia, Ex ic, Ex nA, Ex tb
- CCSA_{US} IS, CCSA_{US} XP, CCSA_{US} NI

SI units

Version w	Version with max. T_m = 440 °C										
T _a 1) [°C]	T6 [85 °C]				T2 [300 °C]	T1 [450°C]					
40	80	95	130	195	290	440					
50 ²⁾	-	95	130	195	290	440					
65	_	-	130	195	290	440					
70	-	-	130	195 ³⁾	290 ³⁾	440 ³⁾					

- The following applies for installations with overvoltage protection in conjunction with temperature class T5, T6 and approval options BA, BB, BD, BH, BJ, B2, IA, IB, ID, IH, IJ, I4, C2: $T_a = T_a 2$ °C
- 2) $T_a = 60$ °C for pulse/frequency/switch output $P_i = 0$ W
- 3) $T_a = 70$ °C for pulse/frequency/switch output $P_i = 0$ W

US units

Version wit	Version with max. T_m = 824 $^{\circ}F$										
T _a 1) [°F]	T6 [185 °F]	T5 [212 °F]	T4 [275 °F]	T3 [392 °F]	T2 [572 °F]	T1 [842 °F]					
104	176	203	266	383	554	824					
122 ²⁾	-	203	266	383	554	824					
149	-	-	266	383	554	824					
158	-	-	266	383 ³⁾	554 ³⁾	824 ³⁾					

- 1) The following applies to installations with overvoltage protection in conjunction with temperature class T5, T6 and approval options BA, BB, BD, BH, BJ, B2, IA, IB, ID, IH, IJ, I4, C2: $T_a = T_a 35.6$ °F
- 2) $T_a = 140$ °F for pulse/frequency/switch output $P_i = 0$ W
- 3) $T_a = 158 \,^{\circ}\text{F}$ for pulse/frequency/switch output $P_i = 0 \,^{\circ}\text{W}$

Remote version

Transmitter

Order code for "Housing", option J "GT20 two-chamber, remote G314, aluminum coated"; option K "GT20 two-chamber, remote G315, 316L"

SI units

Order code for "Output", option	Order code for "Approval", option	T6 [85 °C]	T5 [100 ℃]	T4 [135 ℃]
А	All	40	60	75
В	BA, BB, BD, BH, BJ, B2, IA, IB, ID, IH, IJ, I4, C2	35 ¹⁾	50 ²⁾	70 ³⁾
	BC, BG, BK, B3, IC, IG, IK, I5, C3	40	55	70 ³⁾
С	All	40	55	70 ⁴⁾
D	All	35 ⁵⁾	50 ⁵⁾	65
E G	All	40	55	70 ⁴⁾

- 1) $T_a = 40$ °C for pulse/frequency/switch output $P_i = 0.85$ W
- 2) $T_a = 60$ °C for pulse/frequency/switch output $P_i = 0.85$ W
- 3) $T_a = 75$ °C for pulse/frequency/switch output $P_i = 0.85$ W
- 4) $T_a = 75$ °C for pulse/frequency/switch output $P_i = 0$ W
- The following applies to installations with overvoltage protection in conjunction with temperature class T5, T6 and approval options BA, BB, BD, BH, BJ, B2, IA, IB, ID, IH, IJ, I4, C2: $T_a = T_a 2$ °C

US units

Order code for "Output", option	Order code for "Approval", option	T6 [185 °F]	T5 [212 °F]	T4 [275 °F]
A	All	104	140	167
В	BA, BB, BD, BH, BJ, B2, IA, IB, ID, IH, IJ, I4, C2	95 ¹⁾	122 ²⁾	158 ³⁾
	BC, BG, BK, B3, IC, IG, IK, I5, C3	104	131	158 ³⁾
С	All	104	131	158 ⁴⁾
D	All	95 ⁵⁾	122 ⁵⁾	149
E G	All	104	131	158 ⁴⁾

- 1) $T_a = 104$ °F for pulse/frequency/switch output $P_i = 0.85$ W
- 2) $T_a = 140$ °F for pulse/frequency/switch output $P_i = 0.85$ W
- 3) $T_a = 167$ °F for pulse/frequency/switch output $P_i = 0.85$ W
- 4) $T_a = 167$ °F for pulse/frequency/switch output $P_i = 0$ W
- The following applies to installations with overvoltage protection in conjunction with temperature class T5, T6 and approval options BA, BB, BD, BH, BJ, B2, IA, IB, ID, IH, IJ, I4, C2: $T_a = T_a 35.6$ °F

Sensor

Order code for "Sensor version", option 1 "Volume flow, basis"; option 3 "Mass flow (integrated temperature measurement)"

Order code for "Sensor version", option 2 "Volume flow, high-temperature/low-temperature"

The following temperature tables apply to the low-temperature version $\Rightarrow \triangleq 52$.

SI units

Version v	Version with max. T_m = 280 °C										
T _a [°C]	T6 [85 ℃]	T5 [100°C]	T4 [135 ℃]	T3 [200 ℃]	T2 [300°C]	T1 [450 ℃]					
55	80	95	130	195	280	-					
70	-	95	130	195	280	-					
85	-	-	130	195	280	-					

US units

Version	Version with max. T_m = 536 $^{\circ}F$									
T _a [°F]	T6 [185 °F]	T5 T4 [212 °F] [275 °F]	T4 [275 °F]	T3 [392 °F]	T2 [572 °F]	T1 [842 °F]				
104	176	203	266	383	536	-				
122	-	203	266	383	536	-				
149	-	-	266	383	536	_				

High-temperature version

 ${\it Order\ code\ for\ "Sensor\ version"}, option\ 2\ "Volume\ flow,\ high-temperature/low-temperature"$

SI units

Version v	Version with max. T_m = 440 °C									
T _a [°C]	T6 T5 [85 °C] [100 °C]		T4 [135 ℃]	T3 [200 ℃]	T2 [300 °C]	T1 [450 ℃]				
55	80	95	130	195	290	440				
70	-	95	130	195	290	440				
85	-	-	130	195	290	440				

US units

Version with max. T_m = 824 $^{\circ}F$										
T _a [°F]	T6 [185 °F]	T5 [212 °F]	T4 [275 °F]	T3 [392 °F]	T2 [572 °F]	T1 [842 °F]				
131	176	203	266	383	554	824				
158	_	203	266	383	554	824				
185	-	-	266	383	554	824				

Storage temperature

All components apart from the display modules:

-50 to +80 °C (−58 to +176 °F)

Remote display and operating module DKX001

 $-50 \text{ to } +80 \,^{\circ}\text{C} \, (-58 \text{ to } +176 \,^{\circ}\text{F})$

Climate class

DIN EN 60068-2-38 (test Z/AD)

Degree of protection

Transmitter

• As standard: IP66/67, type 4X enclosure

■ When housing is open: IP20, type 1 enclosure

■ Display module: IP20, type 1 enclosure

Sensor

IP66/67, type 4X enclosure

Device plugs

IP67, only in screwed situation

Vibration resistance

- For compact/remote version made of coated aluminum and remote version made of stainless steel: Acceleration up to 2 q (if gain set to factory setting), 10 to 500 Hz, following IEC 60068-2-6
- For the compact version made of stainless steel: Acceleration up to 1 g (if gain set to factory setting), 10 to 500 Hz, following IEC 60068-2-6

Electromagnetic compatibility (EMC)

As per IEC/EN 61326 and NAMUR Recommendation 21 (NE 21)



For details, refer to the Declaration of Conformity.

Process

Medium temperature range

DSC sensor 2)

Order code for "Sensor version":

- Option 1 "Volume flow, basis":
 - -40 to +260 °C (-40 to +500 °F), stainless steel
- Option 2 "Volume flow, high-temperature/low-temperature":
 -200 to +400 °C (-328 to +752 °F), stainless steel
- Option 3 "Mass flow (integrated temperature measurement)":
 −200 to +400 °C (−328 to +752 °F), stainless steel

Order code for "Sensor option":

Option CD "Harsh environment 3), DSC sensor components Alloy C22".

 $-200 \text{ to } +400 \,^{\circ}\text{C} \, (-328 \text{ to } +752 \,^{\circ}\text{F})$, DSC sensor Alloy C22

Seals

- $-200 \text{ to } +400 \,^{\circ}\text{C} \, (-328 \text{ to } +752 \,^{\circ}\text{F}) \text{ for graphite (standard)}$
- -15 to +175 °C (+5 to +347 °F) for Viton
- -20 to +275 °C (-4 to +527 °F) for Kalrez
- $-200 \text{ to } +260 \,^{\circ}\text{C} \, (-328 \text{ to } +500 \,^{\circ}\text{F}) \text{ for Gylon}$

Pressure-temperature ratings


The following pressure-temperature ratings refer to the entire device and not just the process connection.

The pressure-temperature rating for the specific measuring device is programmed into the software. If values exceed the curve range a warning is displayed. Depending on the system configuration and sensor version, the pressure and temperature are determined by entering, reading in or calculating values.

Capacitance sensor


³⁾ Aggressive atmosphere (salts or chloride in the air)

Process connection: wafer flange to EN 1092-1 (DIN 2501)




■ 16 Process connection material: stainless cast steel, multiple certifications, 1.4408 (CF3M)

Process connection: wafer flange to ASME B16.5



■ 17 Process connection material: stainless cast steel, multiple certifications, 1.4408 (CF3M)

Process connection: wafer flange to JIS B2220



 \blacksquare 18 Process connection material: stainless cast steel, multiple certifications, 1.4408 (CF3M)

Secondary containment pressure rating

The following overpressure resistance values apply to the sensor shaft in the event of a membrane rupture:

Sensor version	Overpressure, sensor shaft in [bar a]		
Volume flow, basis	200		
Volume flow, high-temperature/low-temperature	200		
Mass flow (integrated temperature measurement)	200		

Pressure loss


Thermal insulation

For optimum temperature measurement and mass calculation, heat transfer at the sensor must be avoided for some fluids. This can be ensured by installing thermal insulation. A wide range of materials can be used for the required insulation.

This applies for:

- Compact version
- Remote sensor version

The maximum insulation height permitted is illustrated in the diagram:



A00192

- 1 Maximum insulation height
- ▶ When insulating, ensure that a sufficiently large area of the housing support remains exposed.

The uncovered part serves as a radiator and protects the electronics from overheating and excessive cooling.

Vibrations


The correct operation of the measuring system is not affected by plant vibrations up to $1\,\mathrm{g}$, $10\,\mathrm{to}$ 500 Hz. Therefore no special measures are needed to secure the sensors.

Mechanical construction

Dimensions in SI units

Compact version

Order code for "Housing", option B "GT18, two-chamber, 316L"; option C "GT20, two-chamber, aluminum, coated"



■ 19 Engineering unit mm (in)

Endress+Hauser 55


A002027

DN	Α	B 1)	С	D 2)	Е	F 2)	G ^{3) 4)}	H ^{3) 4)}	L	K	di
[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]
15	162	102	60	165	75	90	252.5	275.9	65	5)	5)
25	162	102	60	165	75	90	262.0	294.4	65	5)	5)
40	162	102	60	165	75	90	270.5	312.0	65	5)	5)
50	162	102	60	165	75	90	277.5	324.0	65	5)	5)
80	162	102	60	165	75	90	291.5	355.5	65	5)	5)
100 ⁶⁾	162	102	60	165	75	90	304.0	383.1	65	5)	5)
100 7)	162	102	60	165	75	90	303.2	382.3	65	5)	5)
150	162	102	60	165	75	90	330.0	438.5	65	5)	5)

- 1)
- For version without local display: values 7 mm For version with overvoltage protection: values + 8 mm 2)
- 3) For version without local display: values - 10 mm
- 4) For high-temperature/low-temperature version: values + 29 mm
- 5) Depends on the particular wafer version
- 6) EN (DIN), ASME
- JIS

Transmitter remote version

 $Order\ code\ for\ "Housing",\ option\ J\ "GT20,\ remote,\ aluminum\ coated";\ option\ K\ "GT18\ remote,\ 316L"$




A 1)	В	C 1)	D ²⁾	E	F 2)	G ³⁾	Н
[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]
162	90	191	165	75	90	254	107

- For device version without local display: value 7 mm $\,$ 1)
- For device version with overvoltage protection (OVP): value + 8 mm 2)
- 3) For device version without local operation: value – 10 mm

Sensor remote version

Order code for "Housing", option J "GT20, remote, aluminum, coated"; option K "GT18, remote, 316L"



20 € Engineering unit mm (in)

DN	Α	В	С	D	E 1)	F 1)	L	К	di
[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]
15	94.3	134.3	107.3	115.8	222.8	246.2	65	2)	2)
25	94.3	134.3	107.3	115.8	232.3	264.7	65	2)	2)
40	94.3	134.3	107.3	115.8	240.8	282.3	65	2)	2)
50	94.3	134.3	107.3	115.8	247.8	294.3	65	2)	2)
80	94.3	134.3	107.3	115.8	261.8	325.8	65	2)	2)
100 ³⁾	94.3	134.3	107.3	115.8	274.3	353.4	65	2)	2)
100 4)	94.3	134.3	107.3	115.8	273.5	352.6	65	2)	2)
150	94.3	134.3	107.3	115.8	300.3	408.8	65	2)	2)

- For high-temperature/low-temperature version: values + 29 mm
- 2) Depends on the particular wafer version
- 3) 4) EN (DIN), ASME
- JIS

Flange connections

Wafer flange

Wafer flange as per EN 1092-1 (DIN 2501): PN 10 to 40 1.4408 (CF3M) Order code for "Process connection", option DDS/DES/D1S/D2S			
DN [mm]	K [mm]	di [mm]	
15	45.0	16.5	
25	64.0	27.6	
40	82.0	42.0	
50	92.0	53.5	
80	127.0	80.3	
100	157.2	104.8	
150	215.9	156.8	

Wafer flange as per ASME B16.5: Class 150 to 300, Schedule 40 1.4408 (CF3M) Order code for "Process connection", option AAS/ABS			
DN [mm]	K [mm]	di [mm]	
15	45.0	16.5	
25	64.0	27.6	
40	82.0	42.0	
50	92.0	53.5	
80	127.0	80.3	
100	157.2	104.8	
150	215.9	156.8	

Wafer flange as per ASME B16.5: Class 150 to 300, Schedule 80 1.4408 (CF3M) Order code for "Process connection", option AFS/AGS			
DN [mm]	K [mm]	di [mm]	
15	45.0	13.9	
25	64.0	24.3	
40	82.0	38.1	
50	92.0	49.3	
80	127.0	73.7	
100	157.2	97.2	
150	215.9	146.3	

Wafer flange as per JIS B2220: 10 to 20K, Schedule 40 1.4408 (CF3M) Order code for "Process connection", option NDS/NES			
DN [mm]	K [mm]	di [mm]	
15 ¹⁾	45.0	16.5	
25 ¹⁾	64.0	27.6	
40 1)	82.0	42.0	
50	92.0	53.5	
80	127.0	80.3	
100	157.2	102.3	
150	215.9	156.8	

1) Not available for JIS B2220, 10K

Wafer flange as per JIS B2220: 10 to 20K, Schedule 80 1.4408 (CF3M) Order code for "Process connection", option NFS/NGS		
DN [mm]	K [mm]	di [mm]
15 ¹⁾	45.0	13.9
25	64.0	24.3


Wafer flange as per JIS B2220: 10 to 20K, Schedule 80 1.4408 (CF3M) Order code for "Process connection", option NFS/NGS		
DN [mm]	K [mm]	di [mm]
40	82.0	38.1
50	92.0	49.3

80 127.0 73.7 100 157.2 97.2 150 215.9 146.3

1) Not available for JIS B2220, 10K

Accessories

Flow conditioner



A000194

As per EN 1092-1 (DIN 2501): PN 10
1.4404 (316, 316L)
Order code for "Accessory enclosed", option PF

DN [mm]	Centering diameter [mm]	D1 ¹⁾ / D2 ²⁾	s [mm]
15	54.3	D2	2.0
25	74.3	D1	3.5
40	95.3	D1	5.3
50	110.0	D2	6.8
80	145.3	D2	10.1
100	165.3	D2	13.3
150	221.0	D2	20.0

- $1) \qquad \hbox{The flow conditioner is fitted at the outer diameter between the bolts.}$
- The flow conditioner is fitted at the indentations between the bolts.

As per EN 1092-1 (DIN 2501): PN 16 1.4404 (316, 316L) Order code for "Accessory enclosed", option PF			
DN [mm]	Centering diameter [mm]	D1 ¹⁾ / D2 ²⁾	s [mm]
15	54.3	D2	2.0
25	74.3	D1	3.5

As per EN 1092-1 (DIN 2501): PN 16 1.4404 (316, 316L) Order code for "Accessory enclosed", option PF

D1 $^{1)}$ / D2 $^{2)}$ DN Centering diameter [mm] [mm] [mm] 40 95.3 D1 5.3 110.0 6.8 80 145.3 D2 10.1 165.3 13.3 100 D2 150 221.0 D2 20.0

- 1) The flow conditioner is fitted at the outer diameter between the bolts.
- 2) The flow conditioner is fitted at the indentations between the bolts.

As per EN 1092-1 (DIN 2501): PN 25 1.4404 (316, 316L) Order code for "Accessory enclosed", option PF

	,,,		
DN [mm]	Centering diameter [mm]	D1 1) / D2 2)	s [mm]
15	54.3	D2	2.0
25	74.3	D1	3.5
40	95.3	D1	5.3
50	110.0	D2	6.8
80	145.3	D2	10.1
100	171.3	D1	13.3
150	227.0	D2	20.0

- 1) The flow conditioner is fitted at the outer diameter between the bolts.
- 2) The flow conditioner is fitted at the indentations between the bolts.

As per EN 1092-1 (DIN 2501): PN 40 1.4404 (316, 316L)			
Order code for "Accessory enclosed", option PF			
DN	C + : 1: +	Da 1) (Da 2)	

DN [mm]	Centering diameter [mm]	D1 ¹⁾ / D2 ²⁾	s [mm]
15	54.3	D2	2.0
25	74.3	D1	3.5
40	95.3	D1	5.3
50	110.0	D2	6.8
80	145.3	D2	10.1
100	171.3	D1	13.3
150	227.0	D2	20.0

- 1) The flow conditioner is fitted at the outer diameter between the bolts.
- 2) The flow conditioner is fitted at the indentations between the bolts.

As per ASME B16.5: Class 150 1.4404 (316, 316L) Order code for "Accessory enclosed", option PF

DN [mm]	Centering diameter [mm]	D1 ¹⁾ / D2 ²⁾	s [mm]
15	50.1	D1	2.0
25	69.2	D2	3.5
40	88.2	D2	5.3
50	106.6	D2	6.8
80	138.4	D1	10.1
100	176.5	D2	13.3
150	223.5	D1	20.0

- 1) The flow conditioner is fitted at the outer diameter between the bolts.
- 2) The flow conditioner is fitted at the indentations between the bolts.

As per ASME B16.5: Class 300	
1.4404 (316, 316L)	
Order code for "Accessory enclosed", option PF	

DN [mm]	Centering diameter [mm]	D1 1) / D2 2)	s [mm]
15	56.5	D1	2.0
25	74.3	D1	3.5
40	97.7	D2	5.3
50	113.0	D1	6.8
80	151.3	D1	10.1
100	182.6	D1	13.3
150	252.0	D1	20.0

- 1) The flow conditioner is fitted at the outer diameter between the bolts.
- 2) The flow conditioner is fitted at the indentations between the bolts.

As per JIS B2220: 10K
1.4404 (316, 316L)
Order code for "Accessory enclosed", option P

DN [mm]	Centering diameter [mm]	D1 ¹⁾ / D2 ²⁾	s [mm]
15	60.3	D2	2.0
25	76.3	D2	3.5
40	91.3	D2	5.3
50	106.6	D2	6.8
80	136.3	D2	10.1
100	161.3	D2	13.3
150	221.0	D2	20.0

- 1) The flow conditioner is fitted at the outer diameter between the bolts.
- 2) The flow conditioner is fitted at the indentations between the bolts.


As per JIS B2220: 20K 1.4404 (316, 316L) Order code for "Accessory enclosed", option PF								
DN [mm]	Centering diameter [mm]	D1 1) / D2 2)	s [mm]					
15	60.3	D2	2.0					
25	76.3	D2	3.5					
40	91.3	D2	5.3					
50	106.6	D2	6.8					
80	142.3	D1	10.1					
100	167.3	D1	13.3					
150	240.0	D1	20.0					

- 1) The flow conditioner is fitted at the outer diameter between the bolts.
- 2) The flow conditioner is fitted at the indentations between the bolts.

Dimensions in US units

Compact version

Order code for "Housing", option B "GT18, two-chamber, 316L"; option C "GT20, two-chamber, aluminum, coated" $\,$



■ 21 Engineering unit mm (in)

DN	Α	B 1)	С	D 2)	Е	F 2)	G ^{3) 4)}	H ^{3) 4)}	L	К	di
[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]
1/2	6.38	4.02	2.36	6.50	2.95	3.54	9.94	10.86	2.56	5)	5)
1	6.38	4.02	2.36	6.50	2.95	3.54	10.31	11.59	2.56	5)	5)
1 ½	6.38	4.02	2.36	6.50	2.95	3.54	10.65	12.28	2.56	5)	5)
2	6.38	4.02	2.36	6.50	2.95	3.54	10.93	12.76	2.56	5)	5)
3	6.38	4.02	2.36	6.50	2.95	3.54	11.48	14.00	2.56	5)	5)
4 ⁶⁾	6.38	4.02	2.36	6.50	2.95	3.54	11.97	15.08	2.56	5)	5)

Endress+Hauser


A0020271

DN	Α	B 1)	С	D 2)	E	F 2)	G ^{3) 4)}	H 3) 4)	L	K	di
[in]	[in]	[in]	[in]	[in]							
4 7)	6.38	4.02	2.36	6.50	2.95	3.54	11.94	15.05	2.56	5)	5)
6	6.38	4.02	2.36	6.50	2.95	3.54	12.99	17.26	2.56	5)	5)

- 1) For version without local display: values 0.28 in
- 2) For version with overvoltage protection: values + 0.31 in
- 3) For version without local display: values 0.39 in
- 4) For high-temperature/low-temperature version: values + 1.14 in
- 5) Depends on the particular wafer version
- 6) EN (DIN), ASME
- 7) JIS

Transmitter remote version

Order code for "Housing", option J "GT20, remote, aluminum coated"; option K "GT18 remote, 316L"




A0020089

A 1)	В	С	D ²⁾	Е	F	G ³⁾	Н
[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]
6.38	3.54	7.52	6.5	2.75	3.54	10.0	4.21

- 1) For device version without local display: value 0.28 in
- 2) For device version with overvoltage protection (OVP): value \pm 0.31 in
- 3) For device version without local operation: value -0.39 in

Sensor remote version

Order code for "Housing", option J "GT20, remote, aluminum, coated"; option K "GT18, remote, 316L"



Engineering unit mm (in)

DN	А	В	С	D	E 1)	F 1)	L	К	di
[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]
1/2	3.71	5.29	4.22	4.56	8.77	9.69	2.56	2)	2)
1	3.71	5.29	4.22	4.56	9.15	10.42	2.56	2)	2)
1 1/2	3.71	5.29	4.22	4.56	9.48	11.11	2.56	2)	2)
2	3.71	5.29	4.22	4.56	9.76	11.59	2.56	2)	2)
3	3.71	5.29	4.22	4.56	10.31	12.83	2.56	2)	2)
4 3)	3.71	5.29	4.22	4.56	10.8	13.91	2.56	2)	2)
4 4)	3.71	5.29	4.22	4.56	10.77	13.88	2.56	2)	2)
6	3.71	5.29	4.22	4.56	11.82	16.09	2.56	2)	2)

- 1) For high-temperature/low-temperature version: values \pm 1.14 in
- 2) 3) 4) Depends on the particular wafer version EN (DIN), ASME
- JIS

Flange connections


Wafer flange

Wafer flange as per ASME B16.5: Class 150 to 300, Schedule 40 1.4408 (CF3M) Order code for "Process connection", option AAS/ABS							
DN [in]	K [in]	di [in]					
1/2	1.77	0.65					
1	2.52	1.09					
1 ½	3.23	1.65					
2	3.62	2.11					
3	5.00	3.16					
4	6.19	4.13					
6	8.51	6.18					

Wafer flange as per ASME B16.5: Class 150 to 300, Schedule 80 1.4408 (CF3M) Order code for "Process connection", option AFS/AGS			
DN K di [in] [in]			
1/2	1.77	0.55	
1	2.52	0.96	
1 ½	3.23	1.50	
2	3.62	1.94	
3	5.00	2.90	
4	6.19	3.83	
6	8.51	5.76	

Accessories

Flow conditioner



As per ASME B16.5: Class 150 1.4404 (316, 316L) Order code for "Accessory enclosed", option PF			
DN [in]	Centering diameter [in]	D1 ¹⁾ / D2 ²⁾	s [in]
1/2	1.97	D1	0.08
1	2.72	D2	0.14
1½	3.47	D2	0.21
2	4.09	D2	0.27
3	5.45	D1	0.40
4	6.95	D2	0.52
6	8.81	D1	0.79

- The flow conditioner is fitted at the outer diameter between the bolts. The flow conditioner is fitted at the indentations between the bolts. 1)
- 2)

As per ASME B16.5: Class 300 1.4404 (316, 316L) Order code for "Accessory enclosed", option PF			
DN [in]	Centering diameter [in]	D1 ¹⁾ / D2 ²⁾	s [in]
1/2	2.22	D1	0.08
1	2.93	D1	0.14
1½	3.85	D2	0.21
2	4.45	D1	0.27
3	5.96	D1	0.40
4	7.19	D1	0.52
6	9.92	D1	0.79

- The flow conditioner is fitted at the outer diameter between the bolts.
- The flow conditioner is fitted at the indentations between the bolts. 2)

Weight **Compact version**

Weight data:

- Including the transmitter:

 - Order code for "Housing", option C: 1.8 kg (4.0 lb)Order code for "Housing", option B: 4.5 kg (9.9 lb)
- Excluding packaging material

Weight in SI units

DN	Weight [kg]		
[mm]	Order code for "Housing", option C Aluminum, AlSi10Mg, coated ¹⁾	Order code for "Housing", option B Stainless steel, 1.4404 (316L) ¹⁾	
15	3.1	5.8	
25	3.3	6.0	
40	3.9	6.6	
50	4.2	6.9	
80	5.6	8.3	
100	6.6	9.3	
150	9.1	11.8	

1) For high-temperature/low-temperature version: values + 0.2 kg

Weight in US units

DN	Weight [lbs]		
[in]	Order code for "Housing", option C Aluminum, AlSi10Mg, coated ¹⁾	Order code for "Housing", option B Stainless steel, 1.4404 (316L) ¹⁾	
1/2	6.9	12.9	
1	7.4	13.3	
1½	8.7	14.6	
2	9.4	15.3	
3	12.4	18.4	

DN	Weight [lbs]	
[in]	Order code for "Housing", option C Aluminum, AlSi10Mg, coated ¹⁾	Order code for "Housing", option B Stainless steel, 1.4404 (316L) ¹⁾
4	14.6	20.6
6	20.2	26.1

1) For high-temperature/low-temperature version: values +0.4 lbs

Transmitter remote version

Wall-mount housing

Depends on the material of the wall-mount housing:

- Aluminum, AlSi10Mg, coated: 2.4 kg (5.2 lb)
- Stainless steel, 1.4404 (316L): 6.0 kg (13.2 lb)

Sensor remote version

Weight data:

- Including the connection housing:
 - Aluminum, AlSi10Mg, coated: 0.8 kg (1.8 lb)
 - Stainless cast steel, 1.4408 (CF3M): 2.0 kg (4.4 lb)
- Excluding the connecting cable
- Excluding packaging material

Weight in SI units

DN	W	Weight [kg]		
[mm]	Connection housing Aluminum, AlSi10Mg, coated ¹⁾	Connection housing Stainless cast steel, 1.4408 (CF3M) ¹⁾		
15	2.1	3.3		
25	2.3	3.5		
40	2.9	4.1		
50	3.2	4.4		
80	4.6	5.8		
100	5.6	6.8		
150	8.1	9.3		

1) For high-temperature/low-temperature version: values + 0.2 kg

Weight in US units

DN	Weight [lbs]	
[in]	Connection housing Aluminum, AlSi10Mg, coated ¹⁾	Connection housing Stainless cast steel, 1.4408 (CF3M) ¹⁾
1/2	4.5	7.3
1	5.0	7.8
1½	6.3	9.1
2	7.0	9.7
3	10.0	12.8
4	12.3	15.0
6	17.3	20.5

1) For high-temperature/low-temperature version: values +0.4 lbs

Accessories

Flow conditioner

Weight in SI units

DN ¹⁾ [mm]	Pressure rating	Weight [kg]
15	PN 10 to 40	0.04
25	PN 10 to 40	0.1
40	PN 10 to 40	0.3
50	PN 10 to 40	0.5
80	PN 10 to 40	1.4
100	PN 10 to 40	2.4
150	PN 10/16 PN 25/40	6.3 7.8

1) EN (DIN)

DN ¹⁾ [mm]	Pressure rating	Weight [kg]
15	Class 150 Class 300	0.03 0.04
25	Class 150 Class 300	0.1
40	Class 150 Class 300	0.3
50	Class 150 Class 300	0.5
80	Class 150 Class 300	1.2 1.4
100	Class 150 Class 300	2.7
150	Class 150 Class 300	6.3 7.8

1) ASME

DN ¹⁾ [mm]	Pressure rating	Weight [kg]
15	20K	0.06
25	20K	0.1
40	20K	0.3
50	10K 20K	0.5
80	10K 20K	1.1
100	10K 20K	1.80
150	10K 20K	4.5 5.5

1) JIS

Weight in US units

DN ¹⁾ [in]	Pressure rating	Weight [lbs]
1/2	Class 150 Class 300	0.07 0.09
1	Class 150 Class 300	0.3
1½	Class 150 Class 300	0.7
2	Class 150 Class 300	1.1
3	Class 150 Class 300	2.6 3.1
4	Class 150 Class 300	6.0
6	Class 150 Class 300	14.0 16.0

1) ASME

Materials

Transmitter housing


Compact version

- Order code for "Housing", option B "Compact, stainless": Stainless steel CF-3M (316L, 1.4404)
- Order code for "Housing", option C "Compact, aluminum coated": Aluminum, AlSi10Mg, coated
- Window material: glass

Remote version

- \blacksquare Order code for "Housing", option J "Remote, aluminum coated": Aluminum, AlSi10Mg, coated
- Order code for "Housing", option **K** "Remote, stainless": For maximum corrosion resistance: stainless steel 1.4404 (316L)
- Window material: glass

Cable entries/cable glands



A002064

■ 23 Possible cable entries/cable glands

- 1 Cable entry in transmitter housing, wall-mount housing or connection housing with internal thread M20 x 1.5
- 2 Cable gland M20 x 1.5
- Adapter for cable entry with internal thread G $\frac{1}{2}$ or NPT $\frac{1}{2}$

Order code for "Housing", option B "Compact, stainless", option K "Remote, stainless"

Cable entry/cable gland	Type of protection	Material
Cable gland M20 × 1.5	 Non-Ex Ex ia Ex ic Ex nA Ex tb 	Stainless steel ,1.4404
Adapter for cable entry with internal thread G ½"	For non-Ex and Ex (except for CSA Ex d/XP)	Stainless steel, 1.4404 (316L)
Adapter for cable entry with internal thread NPT ½"	For non-Ex and Ex	

Order code for "Housing": option C "Compact, aluminum coated", option J "Remote, aluminum coated"

Cable entry/cable gland	Type of protection	Material
Cable gland M20 × 1.5	Non-ExEx iaEx ic	Plastic
	Adapter for cable entry with internal thread G ½"	Nickel-plated brass
Adapter for cable entry with internal thread NPT ½"	For non-Ex and Ex (except for CSA Ex d/XP)	Nickel-plated brass
Thread NPT ½" via adapter	For non-Ex and Ex	

Connecting cable for remote version

- Standard cable: PVC cable with copper shield
- Reinforced cable: PVC cable with copper shield and additional steel wire braided jacket

Sensor connection housing

- Coated aluminum AlSi10Mg
- Stainless cast steel, 1.4408 (CF3M), in compliance with NACE MR0175-2003 and MR0103-2003

Measuring tubes

Pressure ratings up to PN 40, Class 150/300, and JIS 10K/20K:

Stainless cast steel, 1.4408 (CF3M), in compliance with AD2000 (for AD2000 the temperature range is limited to -10 to +400 °C (+14 to +752 °F)) and in compliance with NACE MR0175-2003 and MR0103-2003

DSC sensor

Pressure ratings up to PN 40, Class 150/300, and JIS 10K/20K:

Parts in contact with medium (marked as "wet" on the DSC sensor flange): Stainless steel, 1.4435 (316, 316L), in compliance with NACE MR0175-2003 and MR0103-2003 Parts not in contact with medium:

- Stainless steel 1.4301 (304)
- Order code for "Sensor option", option CD "Harsh environment ⁴⁾, DSC sensor sensor components Alloy C22":

Alloy C22 sensor: UNS N06022 similar to Alloy C22/2.4602, in compliance with NACE MR0175-2003 and MR0103-2003

⁾ Aggressive atmosphere (salts or chloride in the air)

Seals

- Graphite (standard)
 - Sigraflex HochdruckTM with smooth sheet metal insert made of stainless steel, 316/316L (BAMcertified for oxygen applications, "high quality in terms of TA Luft" (German Clean Air Act))
- FPM (Viton)
- Kalrez 6375
- Gylon 3504 (BAM-certified for oxygen applications, "high quality in terms of TA Luft (German Clean Air Act"))

Housing support

Stainless steel, 1.4408 (CF3M)

Accessories

Weather protection cover

Stainless steel 1.4404 (316L)

Flow conditioner

Stainless steel, multiple certifications, 1.4404 (316, 316L), in compliance with NACE MR0175-2003 and MR0103-2003

Operability

Operating concept

Operator-oriented menu structure for user-specific tasks

- Commissioning
- Operation
- Diagnostics
- Expert level

Quick and safe commissioning

- Guided menus ("Make-it-run" wizards) for applications
- Menu guidance with brief explanations of the individual parameter functions

Reliable operation


- Operation in the following languages:
 - Via local display:
 - English, German, French, Spanish, Italian, Dutch, Portuguese, Polish, Russian, Swedish, Turkish, Chinese, Japanese, Korean, Bahasa (Indonesian), Vietnamese, Czech
 - Via "FieldCare" operating tool:
 - English, German, French, Spanish, Italian, Chinese, Japanese
- Uniform operating philosophy applied to device and operating tools
- If replacing the electronic module, transfer the device configuration via the integrated memory (integrated HistoROM) which contains the process and measuring device data and the event logbook. No need to reconfigure.

Efficient diagnostics increase measurement availability

- Troubleshooting measures can be called up via the device and in the operating tools
- \blacksquare Diverse simulation options, logbook for events that occur and optional line recorder functions

Local operation

Via display module



Display elements

- 4-line display
- With order code for "Display; operation", option E:
 White background lighting; switches to red in event of device errors
- Format for displaying measured variables and status variables can be individually configured
- Permitted ambient temperature for the display: -20 to +60 °C (-4 to +140 °F)
 The readability of the display may be impaired at temperatures outside the temperature range.

Operating elements


- With order code for "Display; operation", option **C**: Local operation with 3 push buttons: [⑤], [⑥], [⑥]
- With order code for "Display; operation", option **E**: External operation via touch control; 3 optical keys: ⊙, ⊙, ⊚
- Operating elements also accessible in various hazardous areas

Additional functionality

- Data backup function
 - The device configuration can be saved in the display module.
- Data comparison function
 The device configuration saved in the display module can be compared to the current device configuration.
- Data transfer function

The transmitter configuration can be transmitted to another device using the display module.

Via remote display and operating module FHX50



A0013137


■ 24 Operating options via FHX50

- 1 Housing of remote display and operating module FHX50
- 2 SD02 display and operating module, push buttons: cover must be opened for operation
- 3 SD03 display and operating module, optical buttons: operation possible through cover glass

Remote operation

Via HART protocol

This communication interface is available in device versions with a HART output.




■ 25 Options for remote operation via HART protocol

- 1 Control system (e.g. PLC)
- 2 Transmitter power supply unit, e.g. RN221N (with communication resistor)
- 3 Connection for Commubox FXA195 and Field Communicator 475
- 4 Field Communicator 475
- 5 Computer with operating tool (e.g. FieldCare, AMS Device Manager, SIMATIC PDM)
- 6 Commubox FXA195 (USB)
- 7 Field Xpert SFX350 or SFX370
- 8 VIATOR Bluetooth modem with connecting cable
- 9 Transmitter

Via PROFIBUS PA network

This communication interface is available in device versions with PROFIBUS PA.




■ 26 Options for remote operation via PROFIBUS PA network

- 1 Automation system
- 2 Segment coupler PROFIBUS DP/PA
- 3 Computer with PROFIBUS network card
- 4 PROFIBUS DP network
- 5 PROFIBUS PA network
- 6 Measuring device
- 7 T-box

Via FOUNDATION Fieldbus network

This communication interface is available in device versions with FOUNDATION Fieldbus.




 \blacksquare 27 Options for remote operation via FOUNDATION Fieldbus network

- 1 Automation system
- 2 Computer with FOUNDATION Fieldbus network card
- *3 Industry network*
- 4 High Speed Ethernet FF-HSE network
- 5 Segment coupler FF-HSE/FF-H1
- 6 FOUNDATION Fieldbus FF-H1 network
- 7 Power supply FF-H1 network
- 8 T-box
- 9 Measuring device

Service interface

Via service interface (CDI)



- $1 \qquad \textit{Service interface (CDI = Endress+Hauser Common Data Interface) of the measuring device}$
- 2 Commubox FXA2913 Computer with "Field
- 3 Computer with "FieldCare" operating tool with COM DTM "CDI Communication FXA291"

Certificates and approvals

CE mark

The measuring system is in conformity with the statutory requirements of the applicable EC Directives. These are listed in the corresponding EC Declaration of Conformity along with the standards applied.

Endress+Hauser confirms successful testing of the device by affixing to it the CE mark.

C-Tick symbol

The measuring system meets the EMC requirements of the "Australian Communications and Media Authority (ACMA)".

Ex approval

The measuring device is certified for use in hazardous areas and the relevant safety instructions are provided in the separate "Safety Instructions" (XA) document. Reference is made to this document on the nameplate.



The separate Ex documentation (XA) containing all the relevant explosion protection data is available from your Endress+Hauser sales center.

ATEX, IECEx

Currently, the following versions for use in hazardous areas are available:

Ex d

Category	Type of protection
II2G/Zone 1	Ex d[ia] IIC T6T1
II1/2G/Zone 0/1	Ex d[ia] IIC T6T1

Ex ia

Category	Type of protection
II2G/Zone 1	Ex ia IIC T6T1
II1G/Zone 0	Ex ia IIC T6T1
II1/2G/Zone 0/1	Ex ia IIC T6T1

Ех іс

Category	Type of protection
II3G/Zone 2	Ex ic IIC T6T1
II1/3G/Zone 0/2	Ex ic[ia] IIC T6T1

Ex nA

Category	Type of protection
II3G/Zone 2	Ex nA IIC T6T1

Ex tb

Category	Type of protection
II2D/Zone 21	Ex tb IIIC Txxx

cCSAus

Currently, the following versions for use in hazardous areas are available:

ХР

Category	Type of protection
Class I, II, III Division 1 Groups A-G	XP (Ex d Flameproof version)

IS

Category	Type of protection
Class I, II, III Division 1 Groups A-G	IS (Ex i Intrinsically safe version)

NI

Category	Type of protection
Class I Division 2 Groups ABCD	NI (Non-incentive version), NIFW-Parameter*

^{*=} Entity- und NIFW-Parameter gemäß Control Drawings

NEPSI

Currently, the following versions for use in hazardous areas are available:

Ex d

Category	Type of protection
Zone 1	Ex d[ia] IIC T1 ~ T6 Ex d[ia Ga] IIC T1 ~ T6
Zone 0/1	Ex d[ia] IIC T1 ~ T6 DIP A21 Ex d[ia Ga] IIC T1 ~ T6 DIP A21

Ex ia

Category	Type of protection
Zone 1	Ex ia IIC T1 ~ T6
Zone 0/1	Ex ia IIC T1 ~ T6 DIP A21

Ex ic

Category	Type of protection
II3G/Zone 2	Ex ic IIC T1 ~ T6
II1/3G/Zone 0/2	Ex ic[ia Ga] IIC T1 ~ T6

Ex nA

Category	Type of protection
Zone 2	Ex nA IIC T1 ~ T6 Ex nA ia Ga IIC T1 ~ T6

INMETRO

Currently, the following versions for use in hazardous areas are available:

Ex d

Category	Type of protection
-	Ex d[ia] IIC T6T1

76

Ex ia

Category	Type of protection
-	Ex ia IIC T6T1

Ex nA

Category	Type of protection
-	Ex nA IIC T6T1 Ex nA[ia Ga] IIC T6T1

Functional safety

The measuring device can be used for flow monitoring systems (min., max., range) up to SIL 2 (single-channel architecture) and SIL 3 (multichannel architecture with homogeneous redundancy) and is independently evaluated and certified by the TÜV in accordance with IEC 61508.

The following types of monitoring in safety equipment are possible: Volume flow



Functional Safety Manual with information on the SIL device $\rightarrow riangleq 83$

HART certification

HART interface

The measuring device is certified and registered by the FieldComm Group. The measuring system meets all the requirements of the following specifications:

- Certified according to HART 7
- The device can also be operated with certified devices of other manufacturers (interoperability)

FOUNDATION Fieldbus certification

FOUNDATION Fieldbus interface

The measuring device is certified and registered by the FieldComm Group. The measuring system meets all the requirements of the following specifications:

- Certified in accordance with FOUNDATION Fieldbus H1
- Interoperability Test Kit (ITK), revision version 6.1.1 (certificate available on request)
- Physical Layer Conformance Test
- The device can also be operated with certified devices of other manufacturers (interoperability)

Certification PROFIBUS

PROFIBUS interface

The measuring device is certified and registered by the PROFIBUS User Organization (PNO). The measuring system meets all the requirements of the following specifications:

- Certified in accordance with PROFIBUS PA Profile 3.02
- The device can also be operated with certified devices of other manufacturers (interoperability)

Pressure Equipment Directive

- With the PED/G1/x (x = category) marking on the sensor nameplate, Endress+Hauser confirms compliance with the "Essential Safety Requirements" specified in Annex I of the Pressure Equipment Directive 97/23/EC.
- Devices bearing this marking (PED) are suitable for the following types of medium: Media in Group 1 and 2 with a vapor pressure greater than, or smaller and equal to 0.5 bar (7.3 psi)
- Devices not bearing this marking (PED) are designed and manufactured according to good engineering practice. They meet the requirements of Art.3 Section 3 of the Pressure Equipment Directive 97/23/EC. The range of application is indicated in tables 6 to 9 in Annex II of the Pressure Equipment Directive.

Experience

The Prowirl 200 measuring system is the official successor to Prowirl 72 and Prowirl 73.

Other standards and guidelines

- EN 60529
 - Degrees of protection provided by enclosures (IP code)
- DIN ISO 13359

 $\label{lem:measurement} \mbox{Measurement of conductive liquid flow in closed conduits - Flanged-type electromagnetic flowmeters - Overall length$

■ EN 61010-1

Safety requirements for electrical equipment for measurement, control and laboratory use - general requirements

■ IEC/EN 61326

Emission in accordance with Class A requirements. Electromagnetic compatibility (EMC requirements).

■ NAMUR NE 21

Electromagnetic compatibility (EMC) of industrial process and laboratory control equipment

■ NAMUR NE 32

Data retention in the event of a power failure in field and control instruments with microprocessors

■ NAMUR NE 43

Standardization of the signal level for the breakdown information of digital transmitters with analog output signal.

■ NAMUR NE 53

Software of field devices and signal-processing devices with digital electronics

NAMUR NE 105

Specifications for integrating fieldbus devices in engineering tools for field devices

NAMUR NE 107

Self-monitoring and diagnosis of field devices

■ NAMUR NE 131

Requirements for field devices for standard applications

■ ASME BPVC Section VIII, Division 1

Rules for Construction of Pressure Vessels

Ordering information

Detailed ordering information is available from the following sources:

- In the Product Configurator on the Endress+Hauser website: www.endress.com → Select your country \rightarrow Products \rightarrow Select measuring technology, software or components \rightarrow Select the product (picklists: measurement method, product family etc.) → Device support (right-hand column): Configure the selected product \rightarrow The Product Configurator for the selected product opens.
- From your Endress+Hauser Sales Center: www.addresses.endress.com

Product Configurator - the tool for individual product configuration

- Up-to-the-minute configuration data
- Depending on the device: Direct input of measuring point-specific information such as measuring range or operating language
- Automatic verification of exclusion criteria
- Automatic creation of the order code and its breakdown in PDF or Excel output format
- Ability to order directly in the Endress+Hauser Online Shop

Application packages

Many different application packages are available to enhance the functionality of the device. Such packages might be needed to address safety aspects or specific application requirements.

The application packages can be ordered with the device or subsequently from Endress+Hauser. Detailed information on the order code in question is available from your local Endress+Hauser sales center or on the product page of the Endress+Hauser website: www.endress.com.



Detailed information on the application packages:

- Special Documentation for the device → 🖺 84
- Special Documentation for the device

Diagnostics functions	Package	Description
	HistoROM extended function	Comprises extended functions concerning the event log and the activation of the measured value memory.
		Event log: Memory volume is extended from 20 message entries (basic version) to up to 100 entries.
		 Data logging (line recorder): Memory capacity for up to 1000 measured values is activated. 250 measured values can be output via each of the 4 memory channels. The recording interval can be defined and configured by the user. Data logging is visualized via the local display or FieldCare.
Heartbeat Technology	Package	Description

Package	Description
Heartbeat Verification	Heartbeat Verification Meets the requirement for traceable verification to DIN ISO 9001:2008 Chapter 7.6 a) "Control of monitoring and measuring equipment". Functional testing in the installed state without interrupting the process. Traceable verification results on request, including a report. Simple testing process via local operation or other operating interfaces. Clear measuring point assessment (pass/fail) with high test coverage within the framework of manufacturer specifications. Extension of calibration intervals according to operator's risk assessment.

Air and industrial gases

Package	Description
Air and industrial gases	This application package enables users to calculate the density and energy of air and industrial gases. The calculations are based on time-tested standard calculation methods. It is possible to automatically compensate for the effect of pressure and temperature via an external or constant value.
	With this application package it is possible to output the energy flow, standard volume flow and mass flow of the following fluids: Air Single gas Gas mixture User-specific gas

Natural gas

Package	Description
Natural gas	This application package enables users to calculate the chemical properties (gross calorific value, net calorific value) of natural gases. The calculations are based on time-tested standard calculation methods. It is possible to automatically compensate for the effect of pressure and temperature via an external or constant value. With this application package it is possible to output the energy flow, standard volume flow and mass flow based on the following standard methods:
	Energy can be calculated based on the following standards: • AGA5 • ISO 6976 • GPA 2172
	Density can be calculated based on the following standards: ISO 12213-2 (AGA8-DC92) ISO 12213-3 AGA NX19 AGA8 Gross 1 SGERG 88

Accessories

Various accessories, which can be ordered with the device or subsequently from Endress+Hauser, are available for the device. Detailed information on the order code in question is available from your

local Endress+Hauser sales center or on the product page of the Endress+Hauser website: ${\bf www.endress.com}.$

Device-specific accessories

For the transmitter

Accessories	Description
Prowirl 200 transmitter	Transmitter for replacement or storage. Use the order code to define the following specifications: • Approvals • Output • Display / operation • Housing • Software For details, see Installation Instructions EA01056D
Remote display FHX50	FHX50 housing for accommodating a display module → ■ 72. FHX50 housing suitable for: SD02 display module (push buttons) SD03 display module (touch control) Housing material: Plastic PBT Stainless steel CF-3M (316L, 1.4404) Length of connecting cable: up to max. 60 m (196 ft) (cable lengths available for order: 5 m (16 ft), 10 m (32 ft), 20 m (65 ft), 30 m (98 ft))
	 The measuring device can be ordered with the FHX50 housing and a display module. The following options must be selected in the separate order codes: Order code for measuring device, feature 030:
	The FHX50 housing can also be ordered as a retrofit kit. The measuring device display module is used in the FHX50 housing. The following options must be selected in the order code for the FHX50 housing: Feature 050 (measuring device version): option B "Not prepared for FHX50 display" Feature 020 (display, operation): option A "None, existing displayed used" For details, see Special Documentation SD01007F
	(Order number: FHX50)
Overvoltage protection for 2-wire devices	Ideally, the overvoltage protection module should be ordered directly with the device. See product structure, characteristic 610 "Accessory mounted", option NA "Overvoltage protection". Separate order necessary only if retrofitting.
	 OVP10: For 1-channel devices (characteristic 020, option A): OVP20: For 2-channel devices (characteristic 020, options B, C, E or G)
	For details, see Special Documentation SD01090F.
Weather protection cover	Is used to protect the measuring device from the effects of the weather: e.g. rainwater, excess heating from direct sunlight or extreme cold in winter.
	For details, see Special Documentation SD00333F

Connecting cable for remote version	 Connecting cable available in various lengths: 5 m (16 ft) 10 m (32 ft) 20 m (65 ft) 30 m (98 ft) Reinforced cables available on request. Standard length: 5 m (16 ft) Is always supplied if no other cable length has been ordered.
Post mounting kit	Post mounting kit for transmitter. The post mounting kit can only be ordered together with a transmitter. (Order number: DK8WM-B)

For the sensor

Accessories	Description
Mounting kit	Mounting set for disc (wafer version) comprising: Tie rods Seals Nuts Washers For details, see Installation Instructions EA00075D (Order numbers: see EA00075D)
Flow conditioner	Is used to shorten the necessary inlet run. (Order number: DK7ST)

Communication-specific accessories

Accessories	Description
Commubox FXA195 HART	For intrinsically safe HART communication with FieldCare via the USB interface. For details, see "Technical Information" TI00404F
Commubox FXA291	Connects Endress+Hauser field devices with a CDI interface (= Endress+Hauser Common Data Interface) and the USB port of a computer or laptop. For details, see the "Technical Information" document TI405C/07
HART Loop Converter HMX50	Is used to evaluate and convert dynamic HART process variables to analog current signals or limit values. For details, see "Technical Information" TI00429F and Operating Instructions
Wireless HART adapter SWA70	Is used for the wireless connection of field devices. The WirelessHART adapter can be easily integrated into field devices and existing infrastructures, offers data protection and transmission safety and can be operated in parallel with other wireless networks with minimum cabling complexity. For details, see Operating Instructions BA00061S
Fieldgate FXA320	Gateway for the remote monitoring of connected 4-20 mA measuring devices via a Web browser. For details, see "Technical Information" TI00025S and Operating Instructions BA00053S
Fieldgate FXA520	Gateway for the remote diagnostics and remote configuration of connected HART measuring devices via a Web browser. For details, see "Technical Information" TI00025S and Operating Instructions BA00051S

Field Xpert SFX350	Field Xpert SFX350 is a mobile computer for commissioning and maintenance. It enables efficient device configuration and diagnostics for HART and FOUNDATION Fieldbus devices in the non-Ex area . For details, see Operating Instructions BA01202S
Field Xpert SFX370	Field Xpert SFX370 is a mobile computer for commissioning and maintenance. It enables efficient device configuration and diagnostics for HART and FOUNDATION Fieldbus devices in the non-Ex area and the Ex area . For details, see Operating Instructions BA01202S

Service-specific accessories

Accessories	Description		
Applicator	Software for selecting and sizing Endress+Hauser measuring devices: Calculation of all the necessary data for identifying the optimum flowmeter: e.g. nominal diameter, pressure loss, accuracy or process connections. Graphic illustration of the calculation results		
	Administration, documentation and access to all project-related data and parameters throughout the entire life cycle of a project.		
	Applicator is available: Via the Internet: https://wapps.endress.com/applicator On CD-ROM for local PC installation.		
W@M	Life cycle management for your plant W@M supports you with a wide range of software applications over the entire process: from planning and procurement, to the installation, commissioning and operation of the measuring devices. All the relevant device information, such as the device status, spare parts and device-specific documentation, is available for every device over the entire life cycle. The application already contains the data of your Endress+Hauser device. Endress +Hauser also takes care of maintaining and updating the data records. W@M is available: Via the Internet: www.endress.com/lifecyclemanagement On CD-ROM for local PC installation.		
FieldCare	FDT-based plant asset management tool from Endress+Hauser. It can configure all smart field units in your system and helps you manage them. using the status information, it is also a simple but effective way of checking their status and condition.		
	For details, see Operating Instructions BA00027S and BA00059S		
DeviceCare	Tool for connecting and configuring Endress+Hauser field devices. For details, see Innovation brochure IN01047S		

System components

Accessories	Description	
Memograph M graphic display recorder	The Memograph M graphic display recorder provides information on all relevant measured variables. Measured values are recorded correctly, limit values are monitored and measuring points analyzed. The data are stored in the 256 MB internal memory and also on a SD card or USB stick.	
	For details, see "Technical Information" TI00133R and Operating Instructions BA00247R	
RN221N	Active barrier with power supply for safe separation of 4-20 mA standard signal circuits. Offers bidirectional HART transmission.	
	For details, see "Technical Information" TI00073R and Operating Instructions BA00202R	
RNS221	Supply unit for powering two 2-wire measuring devices solely in the non-Ex area. Bidirectional communication is possible via the HART communication jacks.	
	For details, see "Technical Information" TI00081R and Brief Operating Instructions KA00110R	

Cerabar M	The pressure transmitter for measuring the absolute and gauge pressure of gases, steam and liquids. It can be used to read in the operating pressure value. For details, see "Technical Information" TI00426P, TI00436P and Operating Instructions BA00200P, BA00382P
Cerabar S	The pressure transmitter for measuring the absolute and gauge pressure of gases, steam and liquids. It can be used to read in the operating pressure value. For details, see "Technical Information" TI00383P and Operating Instructions BA00271P

Supplementary documentation



For an overview of the scope of the associated Technical Documentation, refer to the following:

- The *W@M Device Viewer*: Enter the serial number from the nameplate (www.endress.com/deviceviewer)
- The Endress+Hauser Operations App: Enter the serial number from the nameplate or scan the 2-D matrix code (QR code) on the nameplate.

Standard documentation

Brief Operating Instructions

Measuring device	Documentation code
Prowirl D 200	KA01135D

Operating Instructions

Measuring device	Documentation code		
	HART	FOUNDATION Fieldbus	PROFIBUS PA
Prowirl D 200	BA01153D	BA01216D	BA01221D

Description of device parameters

Measuring device	Documentation code		
	HART	FOUNDATION Fieldbus	PROFIBUS PA
Prowirl 200	GP01019D	GP01024D	GP01023D

Supplementary devicedependent documentation

Safety Instructions

Contents	Documentation code
ATEX/IECEx Ex d, Ex tb	XA01148D
ATEX/IECEx Ex ia, Ex tb	XA01151D
ATEX/IECEx Ex ic, Ex nA	XA01152D
_C CSA _{US} XP	XA01153D
_c CSA _{US} IS	XA01154D
NEPSI Ex d	XA01238D
NEPSI Ex i	XA01239D
NEPSI Ex ic, Ex nA	XA01240D
INMETRO Ex d	XA01250D
INMETRO Ex i	XA01042D
INMETRO Ex nA	XA01043D

Special Documentation

Contents	Documentation code
Information on the Pressure Equipment Directive	SD01163D
Functional Safety Manual	SD01162D
Heartbeat Technology	SD01204D
Natural gas	SD01194D
Air + Industrial Gases (Single Gas + Gas Mixtures)	SD01195D

Installation Instructions

Contents	Documentation code
Installation Instructions for spare part sets	Specified for each individual accessory $\rightarrow \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ $

Registered trademarks

HART®

Registered trademark of the HART Communication Foundation, Austin, USA

PROFIBUS®

Registered trademark of the PROFIBUS User Organization, Karlsruhe, Germany

FOUNDATIONTM Fieldbus

Registration-pending trademark of the Fieldbus Foundation, Austin, Texas, USA

KALREZ®, VITON®

Registered trademarks of DuPont Performance Elastomers L.L.C., Wilmington, DE USA

GYLON®

Registered trademark of Garlock Sealing Technologies, Palmyar, NY, USA

Applicator®, FieldCare®, DeviceCare®, Field Xpert™, HistoROM®, Heartbeat Technology™ Registered or registration-pending trademarks of the Endress+Hauser Group

www.addresses.endress.com

